

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580694

Luminaire Tested: **HC445D010-HM44560827-41NDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC445D010-HM44560827-41NDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3946.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580694

CATALOG NUMBER: HC445D010-HM44560827-41NDC

Luminous Intensity Polar Plot





TEST NUMBER: P580694

CATALOG NUMBER: HC445D010-HM44560827-41NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	581180
5°	580441
10°	569129
15°	529201
20°	455124
25°	365611
30°	285438
35°	199846
40°	102567
45°	52069
50°	26078
55°	9742
60°	3947
65°	3123
70°	1947
75°	1287
80°	1918
85°	0



TEST NUMBER: P580694

CATALOG NUMBER: HC445D010-HM44560827-41NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.2	11.2
10°-20°	1143.9	29.0
20°-30°	1232.4	31.2
30°-40°	809.7	20.5
40°-50°	251.8	6.4
50°-60°	49.4	1.3
60°-70°	10.6	0.3
70°-80°	3.9	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2819.5	71.5
0°-40°	3629.2	92.0
0°-60°	3930.4	99.6
0°-90°	3946.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3946.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4712	
5°	4688	443
15°	4144	1144
25°	2686	1232
35°	1327	810
45°	298	252
55°	45	49
65°	11	11
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P580694

CATALOG NUMBER: HC445D010-HM44560827-41NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4711.8
2.5°	4687.9
5°	4687.9
7.5°	4650.6
10°	4544.0
12.5°	4373.4
15°	4144.2
17.5°	3837.7
20°	3467.3
22.5°	3067.5
25°	2686.4
27.5°	2332.0
30°	2004.1
32.5°	1695.0
35°	1327.2
37.5°	924.8
40°	637.0
42.5°	439.7
45°	298.5
47.5°	202.5
50°	135.9
52.5°	85.3
55°	45.3
57.5°	18.6
60°	16.0
62.5°	13.4
65°	10.7
67.5°	8.0
70°	5.4
72.5°	5.4
75°	2.7
77.5°	2.7
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)