

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581291

Luminaire Tested: **HC460D010-HM44560830-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560830-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4693.5 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581291

CATALOG NUMBER: HC460D010-HM44560830-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P581291

CATALOG NUMBER: HC460D010-HM44560830-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	412357
5°	409276
10°	398628
15°	388122
20°	370749
25°	345414
30°	304139
35°	239885
40°	174123
45°	127932
50°	104063
55°	87309
60°	79114
65°	72702
70°	67656
75°	61764
80°	55760
85°	48259



TEST NUMBER: P581291

CATALOG NUMBER: HC460D010-HM44560830-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.7	6.6
10°-20°	852.5	18.2
20°-30°	1155.7	24.6
30°-40°	991.7	21.1
40°-50°	585.5	12.5
50°-60°	371.1	7.9
60°-70°	249.3	5.3
70°-80°	137.6	2.9
80°-90°	38.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2319.8	49.4
0°-40°	3311.5	70.6
0°-60°	4268.1	90.9
0°-90°	4693.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4693.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3343	
5°	3306	312
15°	3039	853
25°	2538	1156
35°	1593	992
45°	733	586
55°	406	371
65°	249	249
75°	130	138
85°	34	39
90°	0	



TEST NUMBER: P581291

CATALOG NUMBER: HC460D010-HM44560830-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3343.1
2.5°	3319.1
5°	3305.5
7.5°	3261.2
10°	3182.7
12.5°	3114.4
15°	3039.4
17.5°	2943.9
20°	2824.5
22.5°	2691.5
25°	2538.0
27.5°	2357.2
30°	2135.4
32.5°	1872.8
35°	1593.1
37.5°	1323.6
40°	1081.4
42.5°	880.1
45°	733.4
47.5°	627.6
50°	542.3
52.5°	470.7
55°	406.0
57.5°	354.8
60°	320.7
62.5°	286.5
65°	249.1
67.5°	218.3
70°	187.6
72.5°	156.9
75°	129.6
77.5°	102.3
80°	78.5
82.5°	54.6
85°	34.1
87.5°	13.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)