

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580725

Luminaire Tested: **HC445D010-HM44560835-41MDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580725  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC445D010-HM44560835-41MDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4375.3 lumens  
Efficiency: N/A  
Efficacy: 99.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580725

CATALOG NUMBER: HC445D010-HM44560835-41MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P580725

CATALOG NUMBER: HC445D010-HM44560835-41MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	566415
5°	554575
10°	524090
15°	489487
20°	447694
25°	399771
30°	335715
35°	236165
40°	145688
45°	87219
50°	51389
55°	25591
60°	13198
65°	8668
70°	5374
75°	4289
80°	2131
85°	4246



TEST NUMBER: P580725

CATALOG NUMBER: HC445D010-HM44560835-41MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	418.3	9.6
10°-20°	1071.5	24.5
20°-30°	1336.3	30.5
30°-40°	984.3	22.5
40°-50°	404.8	9.3
50°-60°	118.3	2.7
60°-70°	30.4	0.7
70°-80°	9.4	0.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2826.1	64.6
0°-40°	3810.4	87.1
0°-60°	4333.5	99.0
0°-90°	4375.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4375.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4592	
5°	4479	418
15°	3833	1072
25°	2937	1336
35°	1568	984
45°	500	405
55°	119	118
65°	30	30
75°	9	9
85°	3	2
90°	0	



TEST NUMBER: P580725

CATALOG NUMBER: HC445D010-HM44560835-41MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4592.1
2.5°	4544.5
5°	4479.0
7.5°	4360.0
10°	4184.4
12.5°	4011.8
15°	3833.2
17.5°	3633.8
20°	3410.7
22.5°	3178.5
25°	2937.4
27.5°	2669.6
30°	2357.1
32.5°	1979.1
35°	1568.4
37.5°	1205.4
40°	904.8
42.5°	669.6
45°	500.0
47.5°	369.0
50°	267.8
52.5°	184.6
55°	119.0
57.5°	71.5
60°	53.5
62.5°	38.7
65°	29.7
67.5°	20.9
70°	14.9
72.5°	11.9
75°	9.0
77.5°	5.9
80°	3.0
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)