

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580744

Luminaire Tested: **HC445D010-HM44560840-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC445D010-HM44560840-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4709.5 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580744

CATALOG NUMBER: HC445D010-HM44560840-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580744

CATALOG NUMBER: HC445D010-HM44560840-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63	63	63	63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58	58	58	58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	610845
5°	599744
10°	568866
15°	531895
20°	483082
25°	427467
30°	355570
35°	256388
40°	160034
45°	92295
50°	52079
55°	24795
60°	14234
65°	10916
70°	7321
75°	4861
80°	4759
85°	4812



TEST NUMBER: P580744

CATALOG NUMBER: HC445D010-HM44560840-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	452.8	9.6
10°-20°	1162.0	24.7
20°-30°	1429.1	30.3
30°-40°	1061.3	22.5
40°-50°	431.5	9.2
50°-60°	119.5	2.5
60°-70°	37.3	0.8
70°-80°	12.4	0.3
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3043.8	64.6
0°-40°	4105.2	87.2
0°-60°	4656.1	98.9
0°-90°	4709.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4709.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4952	
5°	4844	453
15°	4165	1162
25°	3141	1429
35°	1703	1061
45°	529	431
55°	115	119
65°	37	37
75°	10	12
85°	3	4
90°	0	



TEST NUMBER: P580744

CATALOG NUMBER: HC445D010-HM44560840-41NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4952.3
2.5°	4904.8
5°	4843.8
7.5°	4721.6
10°	4541.9
12.5°	4355.3
15°	4165.3
17.5°	3938.1
20°	3680.3
22.5°	3419.1
25°	3140.9
27.5°	2839.1
30°	2496.5
32.5°	2106.4
35°	1702.7
37.5°	1322.8
40°	993.9
42.5°	725.9
45°	529.1
47.5°	379.9
50°	271.4
52.5°	186.6
55°	115.3
57.5°	74.6
60°	57.7
62.5°	47.5
65°	37.4
67.5°	27.2
70°	20.3
72.5°	16.9
75°	10.2
77.5°	6.7
80°	6.7
82.5°	3.4
85°	3.4
87.5°	3.4
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)