

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581318

Luminaire Tested: **HC460D010-HM44560840-41WDWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560840-41WDWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6309.6 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581318

CATALOG NUMBER: HC460D010-HM44560840-41WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P581318

CATALOG NUMBER: HC460D010-HM44560840-41WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59			59
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54			54
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49			49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46			46
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	517990
5°	520451
10°	524027
15°	529265
20°	520439
25°	496508
30°	451096
35°	363870
40°	252457
45°	165733
50°	111048
55°	79030
60°	67544
65°	77606
70°	83199
75°	80159
80°	72168
85°	66374



TEST NUMBER: P581318

CATALOG NUMBER: HC460D010-HM44560840-41WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.6	6.3
10°-20°	1164.4	18.5
20°-30°	1663.6	26.4
30°-40°	1486.1	23.6
40°-50°	762.2	12.1
50°-60°	346.5	5.5
60°-70°	258.4	4.1
70°-80°	175.8	2.8
80°-90°	52.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3228.5	51.2
0°-40°	4714.6	74.7
0°-60°	5823.3	92.3
0°-90°	6309.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6309.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4200	
5°	4203	401
15°	4145	1164
25°	3648	1664
35°	2416	1486
45°	950	762
55°	368	347
65°	266	258
75°	168	176
85°	47	52
90°	0	



TEST NUMBER: P581318

CATALOG NUMBER: HC460D010-HM44560840-41WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	4199.5
2.5°	4183.9
5°	4203.4
7.5°	4203.4
10°	4183.9
12.5°	4164.4
15°	4144.7
17.5°	4086.1
20°	3964.9
22.5°	3816.4
25°	3648.2
27.5°	3437.0
30°	3167.2
32.5°	2823.2
35°	2416.5
37.5°	1982.5
40°	1567.9
42.5°	1223.9
45°	950.1
47.5°	742.9
50°	578.7
52.5°	453.6
55°	367.5
57.5°	309.0
60°	273.8
62.5°	265.9
65°	265.9
67.5°	258.1
70°	230.7
72.5°	199.4
75°	168.2
77.5°	133.0
80°	101.6
82.5°	74.3
85°	46.9
87.5°	19.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)