

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581327

Luminaire Tested: **HC460D010-HM44560840-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581327
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560840-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5379.2 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581327

CATALOG NUMBER: HC460D010-HM44560840-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P581327

CATALOG NUMBER: HC460D010-HM44560840-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	472599
5°	469068
10°	456869
15°	444832
20°	424907
25°	395878
30°	348576
35°	274924
40°	199547
45°	146632
50°	119280
55°	100061
60°	90659
65°	83297
70°	77537
75°	70818
80°	63858
85°	55336



TEST NUMBER: P581327

CATALOG NUMBER: HC460D010-HM44560840-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.2	6.6
10°-20°	977.1	18.2
20°-30°	1324.5	24.6
30°-40°	1136.5	21.1
40°-50°	671.1	12.5
50°-60°	425.3	7.9
60°-70°	285.7	5.3
70°-80°	157.7	2.9
80°-90°	44.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2658.8	49.4
0°-40°	3795.3	70.6
0°-60°	4891.6	90.9
0°-90°	5379.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5379.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3832	
5°	3788	357
15°	3484	977
25°	2909	1324
35°	1826	1137
45°	841	671
55°	465	425
65°	285	286
75°	149	158
85°	39	44
90°	0	



TEST NUMBER: P581327

CATALOG NUMBER: HC460D010-HM44560840-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3831.5
2.5°	3804.1
5°	3788.4
7.5°	3737.6
10°	3647.7
12.5°	3569.4
15°	3483.5
17.5°	3374.0
20°	3237.1
22.5°	3084.7
25°	2908.8
27.5°	2701.6
30°	2447.4
32.5°	2146.4
35°	1825.8
37.5°	1516.9
40°	1239.3
42.5°	1008.7
45°	840.6
47.5°	719.3
50°	621.6
52.5°	539.5
55°	465.3
57.5°	406.6
60°	367.5
62.5°	328.4
65°	285.4
67.5°	250.2
70°	215.0
72.5°	179.8
75°	148.6
77.5°	117.3
80°	89.9
82.5°	62.6
85°	39.1
87.5°	15.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)