

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592949

Luminaire Tested: **HC4R60D010-HM44560850-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P592949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R60D010-HM44560850-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6063.3 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592949

CATALOG NUMBER: HC4R60D010-HM44560850-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P592949

CATALOG NUMBER: HC4R60D010-HM44560850-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	687109
5°	701831
10°	729535
15°	729813
20°	674751
25°	583107
30°	474368
35°	348466
40°	201431
45°	94109
50°	43502
55°	15139
60°	4810
65°	3415
70°	2813
75°	1859
80°	0
85°	0



TEST NUMBER: P592949

CATALOG NUMBER: HC4R60D010-HM44560850-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	546.8	9.0
10°-20°	1583.9	26.1
20°-30°	1950.7	32.2
30°-40°	1424.1	23.5
40°-50°	464.1	7.7
50°-60°	77.6	1.3
60°-70°	12.0	0.2
70°-80°	4.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4081.4	67.3
0°-40°	5505.5	90.8
0°-60°	6047.2	99.7
0°-90°	6063.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6063.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5571	
5°	5668	547
15°	5715	1584
25°	4284	1951
35°	2314	1424
45°	540	464
55°	70	78
65°	12	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P592949

CATALOG NUMBER: HC4R60D010-HM44560850-42RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	5570.6
2.5°	5574.5
5°	5668.3
7.5°	5777.7
10°	5824.7
12.5°	5809.1
15°	5715.2
17.5°	5480.7
20°	5140.5
22.5°	4730.2
25°	4284.5
27.5°	3819.3
30°	3330.6
32.5°	2830.3
35°	2314.2
37.5°	1794.3
40°	1251.0
42.5°	817.0
45°	539.5
47.5°	355.8
50°	226.7
52.5°	132.9
55°	70.4
57.5°	27.4
60°	19.5
62.5°	15.7
65°	11.7
67.5°	7.8
70°	7.8
72.5°	3.9
75°	3.9
77.5°	3.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)