

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580780

Luminaire Tested: **HC445D010-HM44560930-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC445D010-HM44560930-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3483.7 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580780

CATALOG NUMBER: HC445D010-HM44560930-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P580780

CATALOG NUMBER: HC445D010-HM44560930-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63	63	63	63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58	58	58	58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	451840
5°	443636
10°	420797
15°	393447
20°	357334
25°	316207
30°	263020
35°	189667
40°	118363
45°	68292
50°	38513
55°	18343
60°	10509
65°	8055
70°	5410
75°	3574
80°	3552
85°	3538



TEST NUMBER: P580780

CATALOG NUMBER: HC445D010-HM44560930-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.9	9.6
10°-20°	859.5	24.7
20°-30°	1057.1	30.3
30°-40°	785.1	22.5
40°-50°	319.2	9.2
50°-60°	88.4	2.5
60°-70°	27.5	0.8
70°-80°	9.2	0.3
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2251.6	64.6
0°-40°	3036.7	87.2
0°-60°	3444.2	98.9
0°-90°	3483.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3483.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3663	
5°	3583	335
15°	3081	860
25°	2323	1057
35°	1260	785
45°	392	319
55°	85	88
65°	28	28
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P580780

CATALOG NUMBER: HC445D010-HM44560930-41NDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3663.2
2.5°	3628.1
5°	3583.0
7.5°	3492.7
10°	3359.7
12.5°	3221.7
15°	3081.1
17.5°	2913.0
20°	2722.3
22.5°	2529.2
25°	2323.4
27.5°	2100.2
30°	1846.7
32.5°	1558.1
35°	1259.6
37.5°	978.5
40°	735.1
42.5°	537.0
45°	391.5
47.5°	281.1
50°	200.7
52.5°	138.0
55°	85.3
57.5°	55.2
60°	42.6
62.5°	35.1
65°	27.6
67.5°	20.1
70°	15.0
72.5°	12.6
75°	7.5
77.5°	5.0
80°	5.0
82.5°	2.5
85°	2.5
87.5°	2.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)