

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592950

Luminaire Tested: **HC460D010-HM44560850-41MDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560850-41MDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6035.9 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 55
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592950
CATALOG NUMBER: HC460D010-HM44560850-41MDC

Luminous Intensity Polar Plot





TEST NUMBER: P592950

CATALOG NUMBER: HC460D010-HM44560850-41MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	699148
5°	711984
10°	733931
15°	725803
20°	666481
25°	574968
30°	468557
35°	346945
40°	199048
45°	96219
50°	45785
55°	15978
60°	5797
65°	3415
70°	2813
75°	1859
80°	0
85°	0



TEST NUMBER: P592950

CATALOG NUMBER: HC460D010-HM44560850-41MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	553.1	9.2
10°-20°	1575.7	26.1
20°-30°	1924.2	31.9
30°-40°	1414.6	23.4
40°-50°	468.9	7.8
50°-60°	82.8	1.4
60°-70°	12.5	0.2
70°-80°	4.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4053.0	67.1
0°-40°	5467.7	90.6
0°-60°	6019.3	99.7
0°-90°	6035.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6035.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5668	
5°	5750	553
15°	5684	1576
25°	4225	1924
35°	2304	1415
45°	552	469
55°	74	83
65°	12	13
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P592950

CATALOG NUMBER: HC460D010-HM44560850-41MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	5668.2
2.5°	5672.0
5°	5750.3
7.5°	5836.4
10°	5859.8
12.5°	5805.0
15°	5683.8
17.5°	5433.5
20°	5077.5
22.5°	4662.8
25°	4224.7
27.5°	3767.1
30°	3289.8
32.5°	2812.6
35°	2304.1
37.5°	1787.7
40°	1236.2
42.5°	817.6
45°	551.6
47.5°	367.7
50°	238.6
52.5°	140.8
55°	74.3
57.5°	31.2
60°	23.5
62.5°	15.7
65°	11.7
67.5°	7.8
70°	7.8
72.5°	3.9
75°	3.9
77.5°	3.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)