

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580797

Luminaire Tested: **HC445D010-HM44560935-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC445D010-HM44560935-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3840.5 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580797

CATALOG NUMBER: HC445D010-HM44560935-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P580797

CATALOG NUMBER: HC445D010-HM44560935-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	497182
5°	486786
10°	460025
15°	429661
20°	392958
25°	350912
30°	294682
35°	207300
40°	127879
45°	76543
50°	45114
55°	22472
60°	11594
65°	7618
70°	4688
75°	3765
80°	1847
85°	3680



TEST NUMBER: P580797

CATALOG NUMBER: HC445D010-HM44560935-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	367.1	9.6
10°-20°	940.5	24.5
20°-30°	1172.9	30.5
30°-40°	864.0	22.5
40°-50°	355.3	9.3
50°-60°	103.8	2.7
60°-70°	26.7	0.7
70°-80°	8.3	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2480.6	64.6
0°-40°	3344.6	87.1
0°-60°	3803.7	99.0
0°-90°	3840.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3840.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4031	
5°	3932	367
15°	3365	941
25°	2578	1173
35°	1377	864
45°	439	355
55°	104	104
65°	26	27
75°	8	8
85°	3	2
90°	0	



TEST NUMBER: P580797

CATALOG NUMBER: HC445D010-HM44560935-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4030.8
2.5°	3989.0
5°	3931.5
7.5°	3827.0
10°	3672.9
12.5°	3521.4
15°	3364.7
17.5°	3189.6
20°	2993.7
22.5°	2790.0
25°	2578.4
27.5°	2343.2
30°	2069.0
32.5°	1737.2
35°	1376.7
37.5°	1057.9
40°	794.2
42.5°	587.8
45°	438.8
47.5°	323.9
50°	235.1
52.5°	162.0
55°	104.5
57.5°	62.7
60°	47.0
62.5°	34.0
65°	26.1
67.5°	18.3
70°	13.0
72.5°	10.4
75°	7.9
77.5°	5.3
80°	2.6
82.5°	2.6
85°	2.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)