

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592859

Luminaire Tested: **HC4R45D010-HM44560950-42RMDC**

Issue Date: 9/23/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592859  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/23/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC4R45D010-HM44560950-42RMDC  
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4020.4 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592859

CATALOG NUMBER: HC4R45D010-HM44560950-42RMDC

### Luminous Intensity Polar Plot





TEST NUMBER: P592859

CATALOG NUMBER: HC4R45D010-HM44560950-42RMDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	455602
5°	465378
10°	483747
15°	483933
20°	447419
25°	386638
30°	314536
35°	231076
40°	133563
45°	62396
50°	28841
55°	10043
60°	3207
65°	2247
70°	1875
75°	1239
80°	0
85°	0



TEST NUMBER: P592859

CATALOG NUMBER: HC4R45D010-HM44560950-42RMDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	362.6	9.0
10°-20°	1050.3	26.1
20°-30°	1293.4	32.2
30°-40°	944.3	23.5
40°-50°	307.7	7.7
50°-60°	51.4	1.3
60°-70°	8.0	0.2
70°-80°	2.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2706.3	67.3
0°-40°	3650.6	90.8
0°-60°	4009.8	99.7
0°-90°	4020.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4020.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3694	
5°	3759	363
15°	3790	1050
25°	2841	1293
35°	1535	944
45°	358	308
55°	47	51
65°	8	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P592859

CATALOG NUMBER: HC4R45D010-HM44560950-42RMDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3693.7
2.5°	3696.3
5°	3758.6
7.5°	3831.1
10°	3862.3
12.5°	3851.8
15°	3789.7
17.5°	3634.2
20°	3408.6
22.5°	3136.4
25°	2840.9
27.5°	2532.5
30°	2208.4
32.5°	1876.7
35°	1534.6
37.5°	1189.8
40°	829.5
42.5°	541.7
45°	357.7
47.5°	235.8
50°	150.3
52.5°	88.1
55°	46.7
57.5°	18.2
60°	13.0
62.5°	10.3
65°	7.7
67.5°	5.2
70°	5.2
72.5°	2.6
75°	2.6
77.5°	2.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)