

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581339

Luminaire Tested: **HC460D010-HM44560927-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581339
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560927-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4251.4 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581339

CATALOG NUMBER: HC460D010-HM44560927-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581339

CATALOG NUMBER: HC460D010-HM44560927-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	357443
5°	360146
10°	364636
15°	373807
20°	376537
25°	365774
30°	335359
35°	275933
40°	201158
45°	130549
50°	73590
55°	34924
60°	13790
65°	8552
70°	5770
75°	3813
80°	1918
85°	3821



TEST NUMBER: P581339

CATALOG NUMBER: HC460D010-HM44560927-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.7	6.5
10°-20°	825.3	19.4
20°-30°	1224.0	28.8
30°-40°	1130.6	26.6
40°-50°	590.3	13.9
50°-60°	161.8	3.8
60°-70°	31.1	0.7
70°-80°	8.7	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2327.0	54.7
0°-40°	3457.6	81.3
0°-60°	4209.7	99.0
0°-90°	4251.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4251.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2898	
5°	2909	278
15°	2927	825
25°	2688	1224
35°	1832	1131
45°	748	590
55°	162	162
65°	29	31
75°	8	9
85°	3	2
90°	0	



TEST NUMBER: P581339

CATALOG NUMBER: HC460D010-HM44560927-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2897.9
2.5°	2889.9
5°	2908.7
7.5°	2916.6
10°	2911.3
12.5°	2916.6
15°	2927.3
17.5°	2916.6
20°	2868.6
22.5°	2791.5
25°	2687.6
27.5°	2546.3
30°	2354.6
32.5°	2112.2
35°	1832.5
37.5°	1539.5
40°	1249.3
42.5°	982.8
45°	748.4
47.5°	548.7
50°	383.5
52.5°	255.7
55°	162.4
57.5°	95.9
60°	55.9
62.5°	39.9
65°	29.3
67.5°	21.3
70°	16.0
72.5°	10.6
75°	8.0
77.5°	5.3
80°	2.7
82.5°	2.7
85°	2.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)