

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581360

Luminaire Tested: **HC460D010-HM44560930-41NDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581360  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC460D010-HM44560930-41NDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4279.8 lumens  
Efficiency: N/A  
Efficacy: 77.8 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 55  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581360

CATALOG NUMBER: HC460D010-HM44560930-41NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P581360

CATALOG NUMBER: HC460D010-HM44560930-41NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	630370
5°	629559
10°	617287
15°	573984
20°	493623
25°	396545
30°	309608
35°	216771
40°	111246
45°	56465
50°	28285
55°	10580
60°	4292
65°	3386
70°	2092
75°	1382
80°	2060
85°	0



TEST NUMBER: P581360

CATALOG NUMBER: HC460D010-HM44560930-41NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	480.7	11.2
10°-20°	1240.7	29.0
20°-30°	1336.7	31.2
30°-40°	878.2	20.5
40°-50°	273.1	6.4
50°-60°	53.6	1.3
60°-70°	11.4	0.3
70°-80°	4.2	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3058.1	71.5
0°-40°	3936.3	92.0
0°-60°	4263.0	99.6
0°-90°	4279.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4279.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5111	
5°	5085	481
15°	4495	1241
25°	2914	1337
35°	1440	878
45°	324	273
55°	49	54
65°	12	11
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P581360

CATALOG NUMBER: HC460D010-HM44560930-41NDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5110.6
2.5°	5084.6
5°	5084.6
7.5°	5044.1
10°	4928.5
12.5°	4743.5
15°	4494.9
17.5°	4162.4
20°	3760.6
22.5°	3327.1
25°	2913.7
27.5°	2529.3
30°	2173.8
32.5°	1838.4
35°	1439.6
37.5°	1003.0
40°	690.9
42.5°	476.9
45°	323.7
47.5°	219.7
50°	147.4
52.5°	92.5
55°	49.2
57.5°	20.2
60°	17.4
62.5°	14.4
65°	11.6
67.5°	8.7
70°	5.8
72.5°	5.8
75°	2.9
77.5°	2.9
80°	2.9
82.5°	2.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°







(END OF REPORT)