

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580840

Luminaire Tested: **HC450D010-HM44560827-41MDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580840  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC450D010-HM44560827-41MDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4067.2 lumens  
Efficiency: N/A  
Efficacy: 84.7 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580840

CATALOG NUMBER: HC450D010-HM44560827-41MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580840

CATALOG NUMBER: HC450D010-HM44560827-41MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	344813
5°	342997
10°	336730
15°	329636
20°	315540
25°	293411
30°	259688
35°	204966
40°	153368
45°	117989
50°	95716
55°	79395
60°	70208
65°	64968
70°	59974
75°	55092
80°	50006
85°	39910



TEST NUMBER: P580840

CATALOG NUMBER: HC450D010-HM44560827-41MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	261.9	6.4
10°-20°	723.9	17.8
20°-30°	983.0	24.2
30°-40°	851.5	20.9
40°-50°	534.6	13.1
50°-60°	336.3	8.3
60°-70°	220.9	5.4
70°-80°	121.9	3.0
80°-90°	33.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1968.8	48.4
0°-40°	2820.2	69.3
0°-60°	3691.1	90.8
0°-90°	4067.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4067.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2796	
5°	2770	262
15°	2581	724
25°	2156	983
35°	1361	851
45°	676	535
55°	369	336
65°	223	221
75°	116	122
85°	28	33
90°	0	



TEST NUMBER: P580840

CATALOG NUMBER: HC450D010-HM44560827-41MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2795.5
2.5°	2778.7
5°	2770.2
7.5°	2742.0
10°	2688.5
12.5°	2634.9
15°	2581.4
17.5°	2508.1
20°	2403.9
22.5°	2285.5
25°	2155.9
27.5°	2006.4
30°	1823.3
32.5°	1600.7
35°	1361.2
37.5°	1141.3
40°	952.5
42.5°	803.1
45°	676.4
47.5°	580.5
50°	498.8
52.5°	428.3
55°	369.2
57.5°	318.5
60°	284.6
62.5°	253.6
65°	222.6
67.5°	191.6
70°	166.3
72.5°	138.0
75°	115.6
77.5°	90.2
80°	70.4
82.5°	47.9
85°	28.2
87.5°	11.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)