

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580858

Luminaire Tested: **HC450D010-HM44560830-41MDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580858  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC450D010-HM44560830-41MDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4516.3 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580858

CATALOG NUMBER: HC450D010-HM44560830-41MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580858

CATALOG NUMBER: HC450D010-HM44560830-41MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	382889
5°	380860
10°	373917
15°	366030
20°	350377
25°	325802
30°	288358
35°	227582
40°	170307
45°	131002
50°	106270
55°	88148
60°	77954
65°	72148
70°	66574
75°	61144
80°	55618
85°	44297



TEST NUMBER: P580858

CATALOG NUMBER: HC450D010-HM44560830-41MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	290.8	6.4
10°-20°	803.8	17.8
20°-30°	1091.5	24.2
30°-40°	945.5	20.9
40°-50°	593.6	13.1
50°-60°	373.4	8.3
60°-70°	245.3	5.4
70°-80°	135.3	3.0
80°-90°	37.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2186.2	48.4
0°-40°	3131.6	69.3
0°-60°	4098.6	90.8
0°-90°	4516.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4516.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3104	
5°	3076	291
15°	2866	804
25°	2394	1091
35°	1511	945
45°	751	594
55°	410	373
65°	247	245
75°	128	135
85°	31	37
90°	0	



TEST NUMBER: P580858

CATALOG NUMBER: HC450D010-HM44560830-41MDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3104.2
2.5°	3085.4
5°	3076.0
7.5°	3044.8
10°	2985.4
12.5°	2925.9
15°	2866.4
17.5°	2785.0
20°	2669.3
22.5°	2537.8
25°	2393.9
27.5°	2228.1
30°	2024.6
32.5°	1777.4
35°	1511.4
37.5°	1267.4
40°	1057.7
42.5°	891.8
45°	751.0
47.5°	644.6
50°	553.8
52.5°	475.7
55°	409.9
57.5°	353.6
60°	316.0
62.5°	281.6
65°	247.2
67.5°	212.8
70°	184.6
72.5°	153.3
75°	128.3
77.5°	100.2
80°	78.3
82.5°	53.2
85°	31.3
87.5°	12.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)