

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581371

Luminaire Tested: **HC460D010-HM44560935-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560935-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3904.0 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581371

CATALOG NUMBER: HC460D010-HM44560935-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P581371

CATALOG NUMBER: HC460D010-HM44560935-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	389340
5°	389713
10°	390462
15°	396154
20°	386277
25°	362426
30°	320575
35°	243769
40°	153577
45°	88195
50°	46783
55°	19397
60°	5205
65°	4378
70°	3246
75°	2859
80°	2131
85°	4246



TEST NUMBER: P581371

CATALOG NUMBER: HC460D010-HM44560935-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.3	7.7
10°-20°	868.7	22.3
20°-30°	1212.3	31.1
30°-40°	997.6	25.6
40°-50°	411.0	10.5
50°-60°	92.6	2.4
60°-70°	14.9	0.4
70°-80°	5.5	0.1
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2380.4	61.0
0°-40°	3378.0	86.5
0°-60°	3881.5	99.4
0°-90°	3904.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3904.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3156	
5°	3148	299
15°	3102	869
25°	2663	1212
35°	1619	998
45°	506	411
55°	90	93
65°	15	15
75°	6	6
85°	3	2
90°	0	



TEST NUMBER: P581371

CATALOG NUMBER: HC460D010-HM44560935-41WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3156.5
2.5°	3141.5
5°	3147.5
7.5°	3135.5
10°	3117.5
12.5°	3108.3
15°	3102.3
17.5°	3048.2
20°	2942.8
22.5°	2810.5
25°	2663.0
27.5°	2485.5
30°	2250.8
32.5°	1961.9
35°	1618.9
37.5°	1272.8
40°	953.8
42.5°	695.1
45°	505.6
47.5°	361.1
50°	243.8
52.5°	153.4
55°	90.2
57.5°	45.1
60°	21.1
62.5°	18.0
65°	15.0
67.5°	12.1
70°	9.0
72.5°	6.0
75°	6.0
77.5°	3.0
80°	3.0
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)