

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580890

Luminaire Tested: **HC4R50D010-HM44560840-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P580890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R50D010-HM44560840-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5559.6 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580890

CATALOG NUMBER: HC4R50D010-HM44560840-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P580890

CATALOG NUMBER: HC4R50D010-HM44560840-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80																			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74																			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69																			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64																			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60																			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56																			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52																			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	630037
5°	643538
10°	668939
15°	669195
20°	618715
25°	534670
30°	434973
35°	319525
40°	184702
45°	86277
50°	39894
55°	13871
60°	4416
65°	3123
70°	2597
75°	1668
80°	0
85°	0



TEST NUMBER: P580890

CATALOG NUMBER: HC4R50D010-HM44560840-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	501.4	9.0
10°-20°	1452.4	26.1
20°-30°	1788.6	32.2
30°-40°	1305.8	23.5
40°-50°	425.6	7.7
50°-60°	71.1	1.3
60°-70°	11.1	0.2
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3742.4	67.3
0°-40°	5048.2	90.8
0°-60°	5544.9	99.7
0°-90°	5559.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5559.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5108	
5°	5198	501
15°	5240	1452
25°	3929	1789
35°	2122	1306
45°	495	426
55°	64	71
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P580890

CATALOG NUMBER: HC4R50D010-HM44560840-42RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	5107.9
2.5°	5111.5
5°	5197.5
7.5°	5297.9
10°	5340.9
12.5°	5326.6
15°	5240.5
17.5°	5025.4
20°	4713.6
22.5°	4337.2
25°	3928.6
27.5°	3502.0
30°	3054.0
32.5°	2595.1
35°	2122.0
37.5°	1645.3
40°	1147.1
42.5°	749.1
45°	494.6
47.5°	326.2
50°	207.9
52.5°	121.9
55°	64.5
57.5°	25.1
60°	17.9
62.5°	14.4
65°	10.7
67.5°	7.2
70°	7.2
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)