

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581381

Luminaire Tested: **HC460D010-HM44560935-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581381
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560935-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4141.8 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581381

CATALOG NUMBER: HC460D010-HM44560935-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P581381

CATALOG NUMBER: HC460D010-HM44560935-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	363882
5°	361174
10°	351773
15°	342508
20°	327170
25°	304802
30°	268390
35°	211681
40°	153658
45°	112896
50°	91839
55°	77051
60°	69814
65°	64122
70°	59722
75°	54520
80°	49225
85°	42598



TEST NUMBER: P581381

CATALOG NUMBER: HC460D010-HM44560935-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.0	6.6
10°-20°	752.3	18.2
20°-30°	1019.8	24.6
30°-40°	875.1	21.1
40°-50°	516.7	12.5
50°-60°	327.4	7.9
60°-70°	220.0	5.3
70°-80°	121.5	2.9
80°-90°	34.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2047.1	49.4
0°-40°	2922.2	70.6
0°-60°	3766.3	90.9
0°-90°	4141.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4141.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2950	
5°	2917	275
15°	2682	752
25°	2240	1020
35°	1406	875
45°	647	517
55°	358	327
65°	220	220
75°	114	121
85°	30	34
90°	0	



TEST NUMBER: P581381

CATALOG NUMBER: HC460D010-HM44560935-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2950.1
2.5°	2929.0
5°	2917.0
7.5°	2877.9
10°	2808.6
12.5°	2748.4
15°	2682.2
17.5°	2597.9
20°	2492.5
22.5°	2375.1
25°	2239.6
27.5°	2080.1
30°	1884.4
32.5°	1652.6
35°	1405.8
37.5°	1167.9
40°	954.3
42.5°	776.6
45°	647.2
47.5°	553.8
50°	478.6
52.5°	415.4
55°	358.3
57.5°	313.0
60°	283.0
62.5°	252.9
65°	219.7
67.5°	192.7
70°	165.6
72.5°	138.5
75°	114.4
77.5°	90.4
80°	69.3
82.5°	48.2
85°	30.1
87.5°	12.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)