

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580908

Luminaire Tested: **HC4R50D010-HM44560927-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P580908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R50D010-HM44560927-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3786.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580908

CATALOG NUMBER: HC4R50D010-HM44560927-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P580908

CATALOG NUMBER: HC4R50D010-HM44560927-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	429045
5°	438237
10°	455529
15°	455699
20°	421337
25°	364100
30°	296206
35°	217599
40°	125770
45°	58768
50°	27172
55°	9441
60°	3010
65°	2131
70°	1767
75°	1144
80°	0
85°	0



TEST NUMBER: P580908

CATALOG NUMBER: HC4R50D010-HM44560927-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	341.5	9.0
10°-20°	989.0	26.1
20°-30°	1218.0	32.2
30°-40°	889.2	23.5
40°-50°	289.8	7.7
50°-60°	48.4	1.3
60°-70°	7.5	0.2
70°-80°	2.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2548.5	67.3
0°-40°	3437.7	90.8
0°-60°	3775.9	99.7
0°-90°	3786.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3786.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3478	
5°	3539	341
15°	3569	989
25°	2675	1218
35°	1445	889
45°	337	290
55°	44	48
65°	7	8
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P580908

CATALOG NUMBER: HC4R50D010-HM44560927-42RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3478.4
2.5°	3480.9
5°	3539.4
7.5°	3607.7
10°	3637.0
12.5°	3627.3
15°	3568.6
17.5°	3422.2
20°	3209.9
22.5°	2953.6
25°	2675.3
27.5°	2384.8
30°	2079.7
32.5°	1767.2
35°	1445.1
37.5°	1120.4
40°	781.1
42.5°	510.1
45°	336.9
47.5°	222.2
50°	141.6
52.5°	83.0
55°	43.9
57.5°	17.0
60°	12.2
62.5°	9.7
65°	7.3
67.5°	4.9
70°	4.9
72.5°	2.4
75°	2.4
77.5°	2.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)