

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580929

Luminaire Tested: **HC450D010-HM44560930-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC450D010-HM44560930-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4499.8 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580929

CATALOG NUMBER: HC450D010-HM44560930-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P580929

CATALOG NUMBER: HC450D010-HM44560930-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77	77	77	77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71	71	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55	55	55	55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51	51	51	51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47	47	47	47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	363512
5°	368825
10°	380405
15°	406472
20°	430709
25°	425983
30°	382332
35°	297571
40°	201592
45°	125856
50°	54459
55°	18257
60°	4588
65°	3094
70°	1911
75°	1287
80°	1918
85°	0



TEST NUMBER: P580929

CATALOG NUMBER: HC450D010-HM44560930-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.1	6.4
10°-20°	903.6	20.1
20°-30°	1415.8	31.5
30°-40°	1221.9	27.2
40°-50°	561.9	12.5
50°-60°	95.4	2.1
60°-70°	10.8	0.2
70°-80°	3.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2605.5	57.9
0°-40°	3827.4	85.1
0°-60°	4484.7	99.7
0°-90°	4499.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4499.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2947	
5°	2979	286
15°	3183	904
25°	3130	1416
35°	1976	1222
45°	722	562
55°	85	95
65°	11	11
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P580929

CATALOG NUMBER: HC450D010-HM44560930-41WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2947.1
2.5°	2947.1
5°	2978.8
7.5°	3008.1
10°	3037.2
12.5°	3098.3
15°	3183.1
17.5°	3254.7
20°	3281.3
22.5°	3241.4
25°	3130.0
27.5°	2949.7
30°	2684.4
32.5°	2350.2
35°	1976.2
37.5°	1599.5
40°	1252.0
42.5°	957.6
45°	721.5
47.5°	506.7
50°	283.8
52.5°	156.5
55°	84.9
57.5°	42.4
60°	18.6
62.5°	13.3
65°	10.6
67.5°	8.0
70°	5.3
72.5°	5.3
75°	2.7
77.5°	2.7
80°	2.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)