

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581447

Luminaire Tested: **HC407D010-HM40525835-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC407D010-HM40525835-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 946.6 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581447

CATALOG NUMBER: HC407D010-HM40525835-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581447

CATALOG NUMBER: HC407D010-HM40525835-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79583
5°	80184
10°	81186
15°	83220
20°	83850
25°	81440
30°	74675
35°	61436
40°	44779
45°	29061
50°	16388
55°	7785
60°	3059
65°	1897
70°	1262
75°	858
80°	426
85°	849



TEST NUMBER: P581447

CATALOG NUMBER: HC407D010-HM40525835-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.8	6.5
10°-20°	183.7	19.4
20°-30°	272.5	28.8
30°-40°	251.7	26.6
40°-50°	131.4	13.9
50°-60°	36.0	3.8
60°-70°	6.9	0.7
70°-80°	1.9	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.1	54.7
0°-40°	769.8	81.3
0°-60°	937.3	99.0
0°-90°	946.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	946.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	645	
5°	648	62
15°	652	184
25°	598	273
35°	408	252
45°	167	131
55°	36	36
65°	6	7
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P581447

CATALOG NUMBER: HC407D010-HM40525835-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	645.2
2.5°	643.4
5°	647.6
7.5°	649.3
10°	648.2
12.5°	649.3
15°	651.7
17.5°	649.3
20°	638.8
22.5°	621.5
25°	598.4
27.5°	567.0
30°	524.3
32.5°	470.3
35°	408.0
37.5°	342.8
40°	278.1
42.5°	218.8
45°	166.6
47.5°	122.2
50°	85.4
52.5°	56.9
55°	36.2
57.5°	21.4
60°	12.4
62.5°	8.9
65°	6.5
67.5°	4.8
70°	3.5
72.5°	2.4
75°	1.8
77.5°	1.1
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)