

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592574

Luminaire Tested: **HC407D010-HM40525850-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC407D010-HM40525850-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1033.7 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592574

CATALOG NUMBER: HC407D010-HM40525850-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P592574

CATALOG NUMBER: HC407D010-HM40525850-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85			85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77			77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71			71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65			65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60			60
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51			51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47			47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83505
5°	84728
10°	87386
15°	93372
20°	98932
25°	97854
30°	87835
35°	68347
40°	46308
45°	28904
50°	12511
55°	4193
60°	1036
65°	700
70°	469
75°	286
80°	426
85°	0



TEST NUMBER: P592574

CATALOG NUMBER: HC407D010-HM40525850-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.7	6.4
10°-20°	207.6	20.1
20°-30°	325.2	31.5
30°-40°	280.7	27.2
40°-50°	129.1	12.5
50°-60°	21.9	2.1
60°-70°	2.5	0.2
70°-80°	0.9	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.5	57.9
0°-40°	879.2	85.1
0°-60°	1030.2	99.7
0°-90°	1033.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	677	
5°	684	66
15°	731	208
25°	719	325
35°	454	281
45°	166	129
55°	20	22
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P592574

CATALOG NUMBER: HC407D010-HM40525850-41WDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	677.0
2.5°	677.0
5°	684.3
7.5°	691.0
10°	697.7
12.5°	711.7
15°	731.2
17.5°	747.7
20°	753.7
22.5°	744.6
25°	719.0
27.5°	677.6
30°	616.7
32.5°	539.9
35°	453.9
37.5°	367.5
40°	287.6
42.5°	220.0
45°	165.7
47.5°	116.4
50°	65.2
52.5°	36.0
55°	19.5
57.5°	9.8
60°	4.2
62.5°	3.1
65°	2.4
67.5°	1.8
70°	1.3
72.5°	1.3
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)