

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581515

Luminaire Tested: **HC407D010-HM40525935-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC407D010-HM40525935-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 686.7 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581515

CATALOG NUMBER: HC407D010-HM40525935-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P581515

CATALOG NUMBER: HC407D010-HM40525935-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	74	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66				66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52				52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49				49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68469
5°	68533
10°	68674
15°	69671
20°	67941
25°	63734
30°	56373
35°	42869
40°	27002
45°	15507
50°	8232
55°	3419
60°	937
65°	759
70°	577
75°	477
80°	426
85°	849



TEST NUMBER: P581515

CATALOG NUMBER: HC407D010-HM40525935-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	7.7
10°-20°	152.8	22.2
20°-30°	213.2	31.0
30°-40°	175.4	25.5
40°-50°	72.3	10.5
50°-60°	16.3	2.4
60°-70°	2.6	0.4
70°-80°	1.0	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.6	61.0
0°-40°	594.1	86.5
0°-60°	682.6	99.4
0°-90°	686.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	555	
5°	554	53
15°	546	153
25°	468	213
35°	285	175
45°	89	72
55°	16	16
65°	3	3
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P581515

CATALOG NUMBER: HC407D010-HM40525935-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	555.1
2.5°	552.5
5°	553.5
7.5°	551.4
10°	548.3
12.5°	546.7
15°	545.6
17.5°	536.1
20°	517.6
22.5°	494.2
25°	468.3
27.5°	437.1
30°	395.8
32.5°	345.0
35°	284.7
37.5°	223.8
40°	167.7
42.5°	122.2
45°	88.9
47.5°	63.5
50°	42.9
52.5°	27.0
55°	15.9
57.5°	8.0
60°	3.8
62.5°	3.2
65°	2.6
67.5°	2.2
70°	1.6
72.5°	1.0
75°	1.0
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)