

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581524

Luminaire Tested: **HC407D010-HM40525935-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581524
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC407D010-HM40525935-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 764.4 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581524

CATALOG NUMBER: HC407D010-HM40525935-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581524

CATALOG NUMBER: HC407D010-HM40525935-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64806
5°	64459
10°	63288
15°	61946
20°	59304
25°	55133
30°	48810
35°	38518
40°	28822
45°	22171
50°	17999
55°	14924
60°	13198
65°	12229
70°	11288
75°	10342
80°	9376
85°	7501



TEST NUMBER: P581524

CATALOG NUMBER: HC407D010-HM40525935-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.2	6.4
10°-20°	136.0	17.8
20°-30°	184.7	24.2
30°-40°	160.0	20.9
40°-50°	100.5	13.1
50°-60°	63.2	8.3
60°-70°	41.5	5.4
70°-80°	22.9	3.0
80°-90°	6.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.0	48.4
0°-40°	530.0	69.3
0°-60°	693.7	90.7
0°-90°	764.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	764.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	525	
5°	521	49
15°	485	136
25°	405	185
35°	256	160
45°	127	100
55°	69	63
65°	42	42
75°	22	23
85°	5	6
90°	0	



TEST NUMBER: P581524

CATALOG NUMBER: HC407D010-HM40525935-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	525.4
2.5°	522.2
5°	520.6
7.5°	515.3
10°	505.3
12.5°	495.1
15°	485.1
17.5°	471.4
20°	451.8
22.5°	429.5
25°	405.1
27.5°	377.1
30°	342.7
32.5°	300.8
35°	255.8
37.5°	214.5
40°	179.0
42.5°	150.9
45°	127.1
47.5°	109.1
50°	93.8
52.5°	80.5
55°	69.4
57.5°	59.9
60°	53.5
62.5°	47.7
65°	41.9
67.5°	36.0
70°	31.3
72.5°	25.9
75°	21.7
77.5°	17.0
80°	13.2
82.5°	9.0
85°	5.3
87.5°	2.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)