

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581525

Luminaire Tested: **HC407D010-HM40525935-41NDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581525  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC407D010-HM40525935-41NDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 728.5 lumens  
Efficiency: N/A  
Efficacy: 91.1 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581525

CATALOG NUMBER: HC407D010-HM40525935-41NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581525

CATALOG NUMBER: HC407D010-HM40525935-41NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	63992
5°	63518
10°	61860
15°	60235
20°	57545
25°	53609
30°	47200
35°	37223
40°	27035
45°	19851
50°	16157
55°	13548
60°	12261
65°	11295
70°	10495
75°	9579
80°	8666
85°	7501



TEST NUMBER: P581525

CATALOG NUMBER: HC407D010-HM40525935-41NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.4	6.6
10°-20°	132.3	18.2
20°-30°	179.4	24.6
30°-40°	153.9	21.1
40°-50°	90.9	12.5
50°-60°	57.6	7.9
60°-70°	38.7	5.3
70°-80°	21.4	2.9
80°-90°	6.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.0	49.4
0°-40°	513.9	70.5
0°-60°	662.4	90.9
0°-90°	728.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	728.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	519	
5°	513	48
15°	472	132
25°	394	179
35°	247	154
45°	114	91
55°	63	58
65°	39	39
75°	20	21
85°	5	6
90°	0	



TEST NUMBER: P581525

CATALOG NUMBER: HC407D010-HM40525935-41NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	518.8
2.5°	515.1
5°	513.0
7.5°	506.1
10°	493.9
12.5°	483.3
15°	471.7
17.5°	456.9
20°	438.4
22.5°	417.6
25°	393.9
27.5°	365.9
30°	331.4
32.5°	290.6
35°	247.2
37.5°	205.4
40°	167.9
42.5°	136.6
45°	113.8
47.5°	97.4
50°	84.2
52.5°	73.1
55°	63.0
57.5°	55.1
60°	49.7
62.5°	44.5
65°	38.7
67.5°	33.9
70°	29.1
72.5°	24.4
75°	20.1
77.5°	15.9
80°	12.2
82.5°	8.4
85°	5.3
87.5°	2.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)