

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581055

Luminaire Tested: **HC405D010-HM40525927-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC405D010-HM40525927-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 579.6 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581055

CATALOG NUMBER: HC405D010-HM40525927-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P581055

CATALOG NUMBER: HC405D010-HM40525927-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77	77	77	77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71	71	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51	51	51	51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47	47	47	47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46834
5°	47509
10°	48997
15°	52356
20°	55484
25°	54874
30°	49251
35°	38337
40°	25972
45°	16223
50°	7004
55°	2344
60°	592
65°	409
70°	252
75°	143
80°	213
85°	0



TEST NUMBER: P581055

CATALOG NUMBER: HC405D010-HM40525927-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	6.4
10°-20°	116.4	20.1
20°-30°	182.4	31.5
30°-40°	157.4	27.2
40°-50°	72.4	12.5
50°-60°	12.3	2.1
60°-70°	1.4	0.2
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	335.6	57.9
0°-40°	493.0	85.1
0°-60°	577.7	99.7
0°-90°	579.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	579.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	380	
5°	384	37
15°	410	116
25°	403	182
35°	255	157
45°	93	72
55°	11	12
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P581055

CATALOG NUMBER: HC405D010-HM40525927-41WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	379.7
2.5°	379.7
5°	383.7
7.5°	387.5
10°	391.2
12.5°	399.1
15°	410.0
17.5°	419.3
20°	422.7
22.5°	417.6
25°	403.2
27.5°	380.0
30°	345.8
32.5°	302.7
35°	254.6
37.5°	206.0
40°	161.3
42.5°	123.4
45°	93.0
47.5°	65.3
50°	36.5
52.5°	20.2
55°	10.9
57.5°	5.4
60°	2.4
62.5°	1.7
65°	1.4
67.5°	1.0
70°	0.7
72.5°	0.7
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)