

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581670

Luminaire Tested: **HC610D010-HM60525935-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC610D010-HM60525935-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1041.7 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581670

CATALOG NUMBER: HC610D010-HM60525935-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581670

CATALOG NUMBER: HC610D010-HM60525935-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 103 | 101 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | 92 | 92 | 92 |
| 2 | 106 | 101 | 96 | 93 | 104 | 99 | 95 | 92 | 96 | 92 | 90 | 93 | 90 | 88 | 90 | 88 | 86 | 84 | 84 | 84 | 84 |
| 3 | 100 | 93 | 87 | 83 | 98 | 91 | 86 | 82 | 89 | 84 | 81 | 86 | 83 | 80 | 84 | 81 | 78 | 77 | 77 | 77 | 77 |
| 4 | 94 | 86 | 79 | 75 | 92 | 85 | 79 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 72 | 70 | 70 | 70 | 70 |
| 5 | 89 | 79 | 73 | 68 | 87 | 78 | 72 | 68 | 76 | 71 | 67 | 75 | 70 | 66 | 73 | 69 | 66 | 64 | 64 | 64 | 64 |
| 6 | 83 | 73 | 67 | 62 | 82 | 73 | 66 | 62 | 71 | 65 | 61 | 70 | 65 | 61 | 68 | 64 | 60 | 59 | 59 | 59 | 59 |
| 7 | 79 | 68 | 62 | 57 | 77 | 68 | 61 | 57 | 66 | 60 | 56 | 65 | 60 | 56 | 64 | 59 | 56 | 54 | 54 | 54 | 54 |
| 8 | 74 | 64 | 57 | 52 | 73 | 63 | 57 | 52 | 62 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 51 | 50 | 50 | 50 | 50 |
| 9 | 70 | 59 | 53 | 48 | 69 | 59 | 53 | 48 | 58 | 52 | 48 | 57 | 52 | 48 | 56 | 51 | 48 | 46 | 46 | 46 | 46 |
| 10 | 66 | 56 | 49 | 45 | 65 | 55 | 49 | 45 | 54 | 49 | 45 | 53 | 48 | 45 | 53 | 48 | 44 | 43 | 43 | 43 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 40797 |
| 5° | 41063 |
| 10° | 41538 |
| 15° | 42395 |
| 20° | 42628 |
| 25° | 41301 |
| 30° | 37468 |
| 35° | 30463 |
| 40° | 20216 |
| 45° | 11249 |
| 50° | 6311 |
| 55° | 3508 |
| 60° | 1941 |
| 65° | 1466 |
| 70° | 1010 |
| 75° | 741 |
| 80° | 442 |
| 85° | 440 |



TEST NUMBER: P581670

CATALOG NUMBER: HC610D010-HM60525935-61WDH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 71.2 | 6.8 |
| 10°-20° | 210.6 | 20.2 |
| 20°-30° | 310.4 | 29.8 |
| 30°-40° | 277.6 | 26.7 |
| 40°-50° | 120.4 | 11.6 |
| 50°-60° | 35.4 | 3.4 |
| 60°-70° | 11.3 | 1.1 |
| 70°-80° | 4.0 | 0.4 |
| 80°-90° | 0.6 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 592.3 | 56.9 |
| 0°-40° | 869.9 | 83.5 |
| 0°-60° | 1025.8 | 98.5 |
| 0°-90° | 1041.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1041.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 744 | |
| 5° | 746 | 71 |
| 15° | 747 | 211 |
| 25° | 683 | 310 |
| 35° | 455 | 278 |
| 45° | 145 | 120 |
| 55° | 37 | 35 |
| 65° | 11 | 11 |
| 75° | 4 | 4 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P581670

CATALOG NUMBER: HC610D010-HM60525935-61WDH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 744.2 |
| 2.5° | 742.0 |
| 5° | 746.2 |
| 7.5° | 747.7 |
| 10° | 746.2 |
| 12.5° | 746.2 |
| 15° | 747.0 |
| 17.5° | 742.7 |
| 20° | 730.7 |
| 22.5° | 710.3 |
| 25° | 682.8 |
| 27.5° | 644.1 |
| 30° | 591.9 |
| 32.5° | 529.9 |
| 35° | 455.2 |
| 37.5° | 369.9 |
| 40° | 282.5 |
| 42.5° | 206.5 |
| 45° | 145.1 |
| 47.5° | 103.6 |
| 50° | 74.0 |
| 52.5° | 52.9 |
| 55° | 36.7 |
| 57.5° | 24.7 |
| 60° | 17.7 |
| 62.5° | 14.2 |
| 65° | 11.3 |
| 67.5° | 8.5 |
| 70° | 6.3 |
| 72.5° | 5.0 |
| 75° | 3.5 |
| 77.5° | 2.8 |
| 80° | 1.4 |
| 82.5° | 0.7 |
| 85° | 0.7 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)