

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581661

Luminaire Tested: **HC610D010-HM60525935-61MDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581661  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC610D010-HM60525935-61MDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 972.7 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581661

CATALOG NUMBER: HC610D010-HM60525935-61MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581661

CATALOG NUMBER: HC610D010-HM60525935-61MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	36203
5°	36072
10°	35470
15°	34847
20°	33638
25°	31901
30°	29011
35°	23182
40°	15472
45°	11024
50°	9194
55°	8009
60°	7576
65°	7121
70°	6556
75°	6121
80°	5588
85°	4843



TEST NUMBER: P581661

CATALOG NUMBER: HC610D010-HM60525935-61MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.0	6.4
10°-20°	172.4	17.7
20°-30°	240.9	24.8
30°-40°	212.2	21.8
40°-50°	114.7	11.8
50°-60°	76.7	7.9
60°-70°	54.3	5.6
70°-80°	30.6	3.1
80°-90°	8.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	475.3	48.9
0°-40°	687.5	70.7
0°-60°	878.9	90.4
0°-90°	972.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	972.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	660	
5°	656	62
15°	614	172
25°	527	241
35°	346	212
45°	142	115
55°	84	77
65°	55	54
75°	29	31
85°	8	9
90°	0	



TEST NUMBER: P581661

CATALOG NUMBER: HC610D010-HM60525935-61MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	660.4
2.5°	656.9
5°	655.5
7.5°	649.2
10°	637.2
12.5°	626.0
15°	614.0
17.5°	597.8
20°	576.6
22.5°	553.4
25°	527.4
27.5°	497.1
30°	458.3
32.5°	410.5
35°	346.4
37.5°	276.8
40°	216.2
42.5°	170.4
45°	142.2
47.5°	123.3
50°	107.8
52.5°	95.1
55°	83.8
57.5°	76.1
60°	69.1
62.5°	61.9
65°	54.9
67.5°	47.9
70°	40.9
72.5°	34.5
75°	28.9
77.5°	23.2
80°	17.7
82.5°	12.7
85°	7.7
87.5°	3.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)