

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592550

Luminaire Tested: **HC405D010-HM40525950-41MDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592550  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC405D010-HM40525950-41MDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 609.8 lumens  
Efficiency: N/A  
Efficacy: 101.6 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592550

CATALOG NUMBER: HC405D010-HM40525950-41MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P592550

CATALOG NUMBER: HC405D010-HM40525950-41MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	78	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	78929
5°	77274
10°	73020
15°	68203
20°	62376
25°	55704
30°	46787
35°	32916
40°	20304
45°	12158
50°	7158
55°	3570
60°	1850
65°	1226
70°	721
75°	572
80°	355
85°	708



TEST NUMBER: P592550

CATALOG NUMBER: HC405D010-HM40525950-41MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.3	9.6
10°-20°	149.3	24.5
20°-30°	186.2	30.5
30°-40°	137.2	22.5
40°-50°	56.4	9.3
50°-60°	16.5	2.7
60°-70°	4.3	0.7
70°-80°	1.3	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.8	64.6
0°-40°	531.0	87.1
0°-60°	603.9	99.0
0°-90°	609.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	609.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	640	
5°	624	58
15°	534	149
25°	409	186
35°	219	137
45°	70	56
55°	17	17
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P592550

CATALOG NUMBER: HC405D010-HM40525950-41MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	639.9
2.5°	633.3
5°	624.1
7.5°	607.6
10°	583.0
12.5°	559.0
15°	534.1
17.5°	506.3
20°	475.2
22.5°	442.9
25°	409.3
27.5°	372.1
30°	328.5
32.5°	275.8
35°	218.6
37.5°	168.0
40°	126.1
42.5°	93.3
45°	69.7
47.5°	51.4
50°	37.3
52.5°	25.8
55°	16.6
57.5°	10.0
60°	7.5
62.5°	5.4
65°	4.2
67.5°	3.0
70°	2.0
72.5°	1.7
75°	1.2
77.5°	0.8
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)