

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581807

Luminaire Tested: **HC615D010-HM60525935-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC615D010-HM60525935-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1397.2 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581807

CATALOG NUMBER: HC615D010-HM60525935-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P581807

CATALOG NUMBER: HC615D010-HM60525935-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61
8	79	70	64	59	78	69	63	59	68	63	59	67	62	59	66	62	59	57
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85530
5°	85169
10°	83154
15°	78933
20°	70362
25°	59266
30°	47216
35°	33689
40°	18113
45°	7760
50°	3531
55°	1290
60°	636
65°	506
70°	449
75°	191
80°	284
85°	0



TEST NUMBER: P581807

CATALOG NUMBER: HC615D010-HM60525935-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.1	10.5
10°-20°	385.5	27.6
20°-30°	446.5	32.0
30°-40°	308.8	22.1
40°-50°	89.2	6.4
50°-60°	15.4	1.1
60°-70°	3.9	0.3
70°-80°	1.5	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	978.2	70.0
0°-40°	1286.9	92.1
0°-60°	1391.4	99.6
0°-90°	1397.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1397.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1560	
5°	1548	146
15°	1391	386
25°	980	447
35°	503	309
45°	100	89
55°	14	15
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581807

CATALOG NUMBER: HC615D010-HM60525935-61NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1560.2
2.5°	1553.5
5°	1547.7
7.5°	1530.4
10°	1493.8
12.5°	1449.5
15°	1390.8
17.5°	1308.1
20°	1206.1
22.5°	1093.5
25°	979.8
27.5°	863.4
30°	745.9
32.5°	628.6
35°	503.4
37.5°	373.4
40°	253.1
42.5°	159.8
45°	100.1
47.5°	64.5
50°	41.4
52.5°	25.0
55°	13.5
57.5°	7.7
60°	5.8
62.5°	4.8
65°	3.9
67.5°	2.8
70°	2.8
72.5°	1.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)