

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581803

Luminaire Tested: **HC615D010-HM60525935-61MDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581803  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC615D010-HM60525935-61MDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1517.5 lumens  
Efficiency: N/A  
Efficacy: 108.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581803

CATALOG NUMBER: HC615D010-HM60525935-61MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P581803

CATALOG NUMBER: HC615D010-HM60525935-61MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72067
5°	73189
10°	77353
15°	86130
20°	89322
25°	73286
30°	51356
35°	35034
40°	18248
45°	6412
50°	2874
55°	918
60°	526
65°	363
70°	305
75°	191
80°	0
85°	0



TEST NUMBER: P581803

CATALOG NUMBER: HC615D010-HM60525935-61MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.8	8.5
10°-20°	426.8	28.1
20°-30°	543.4	35.8
30°-40°	323.9	21.3
40°-50°	78.5	5.2
50°-60°	12.1	0.8
60°-70°	2.9	0.2
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1099.1	72.4
0°-40°	1423.0	93.8
0°-60°	1513.6	99.7
0°-90°	1517.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1315	
5°	1330	129
15°	1518	427
25°	1212	543
35°	524	324
45°	83	79
55°	10	12
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581803

CATALOG NUMBER: HC615D010-HM60525935-61MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1314.6
2.5°	1314.6
5°	1330.0
7.5°	1354.1
10°	1389.6
12.5°	1445.4
15°	1517.6
17.5°	1562.8
20°	1531.1
22.5°	1408.9
25°	1211.6
27.5°	994.0
30°	811.3
32.5°	663.1
35°	523.5
37.5°	385.9
40°	255.0
42.5°	137.6
45°	82.7
47.5°	52.0
50°	33.7
52.5°	20.2
55°	9.6
57.5°	5.8
60°	4.8
62.5°	3.9
65°	2.8
67.5°	1.9
70°	1.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)