

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593111

Luminaire Tested: **HC6R15D010-HM60525950-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R15D010-HM60525950-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1535.6 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593111

CATALOG NUMBER: HC6R15D010-HM60525950-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P593111

CATALOG NUMBER: HC6R15D010-HM60525950-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57		
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53		
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71222
5°	72782
10°	77147
15°	86238
20°	90296
25°	75283
30°	52692
35°	35489
40°	18277
45°	6342
50°	2823
55°	937
60°	428
65°	389
70°	305
75°	212
80°	316
85°	0



TEST NUMBER: P593111

CATALOG NUMBER: HC6R15D010-HM60525950-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.2	8.3
10°-20°	428.1	27.9
20°-30°	556.4	36.2
30°-40°	328.7	21.4
40°-50°	78.4	5.1
50°-60°	11.6	0.8
60°-70°	2.9	0.2
70°-80°	1.2	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1112.7	72.5
0°-40°	1441.4	93.9
0°-60°	1531.4	99.7
0°-90°	1535.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1535.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1299	
5°	1323	128
15°	1520	428
25°	1245	556
35°	530	329
45°	82	78
55°	10	12
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P593111

CATALOG NUMBER: HC6R15D010-HM60525950-62RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1299.2
2.5°	1302.2
5°	1322.6
7.5°	1348.9
10°	1385.9
12.5°	1444.5
15°	1519.5
17.5°	1570.2
20°	1547.8
22.5°	1434.8
25°	1244.6
27.5°	1027.3
30°	832.4
32.5°	673.5
35°	530.3
37.5°	389.9
40°	255.4
42.5°	139.4
45°	81.8
47.5°	50.7
50°	33.1
52.5°	19.5
55°	9.8
57.5°	4.9
60°	3.9
62.5°	3.9
65°	3.0
67.5°	1.9
70°	1.9
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)