

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592917

Luminaire Tested: **HC455D010-HM44560850-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592917
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC455D010-HM44560850-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5425.8 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592917

CATALOG NUMBER: HC455D010-HM44560850-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P592917

CATALOG NUMBER: HC455D010-HM44560850-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	460005
5°	457565
10°	449204
15°	439737
20°	420930
25°	391415
30°	346440
35°	273433
40°	204603
45°	157377
50°	127685
55°	105910
60°	93669
65°	86683
70°	79990
75°	73440
80°	66699
85°	53213



TEST NUMBER: P592917

CATALOG NUMBER: HC455D010-HM44560850-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.4	6.4
10°-20°	965.7	17.8
20°-30°	1311.3	24.2
30°-40°	1135.9	20.9
40°-50°	713.1	13.1
50°-60°	448.6	8.3
60°-70°	294.7	5.4
70°-80°	162.5	3.0
80°-90°	44.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2626.4	48.4
0°-40°	3762.3	69.3
0°-60°	4924.1	90.8
0°-90°	5425.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5425.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3729	
5°	3696	349
15°	3444	966
25°	2876	1311
35°	1816	1136
45°	902	713
55°	492	449
65°	297	295
75°	154	163
85°	38	44
90°	0	



TEST NUMBER: P592917

CATALOG NUMBER: HC455D010-HM44560850-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3729.4
2.5°	3706.9
5°	3695.5
7.5°	3657.9
10°	3586.5
12.5°	3515.1
15°	3443.6
17.5°	3345.9
20°	3206.8
22.5°	3048.9
25°	2876.0
27.5°	2676.7
30°	2432.4
32.5°	2135.4
35°	1815.9
37.5°	1522.6
40°	1270.7
42.5°	1071.4
45°	902.2
47.5°	774.4
50°	665.4
52.5°	571.4
55°	492.5
57.5°	424.8
60°	379.7
62.5°	338.4
65°	297.0
67.5°	255.6
70°	221.8
72.5°	184.2
75°	154.1
77.5°	120.3
80°	93.9
82.5°	63.9
85°	37.6
87.5°	15.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)