

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581214

Luminaire Tested: **HC4R55D010-HM44560930-42RMDC**

Issue Date: 9/23/2021

Test Information

Test Method: LM-41-14
Report Number: P581214
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/23/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC4R55D010-HM44560930-42RMDC
Description: HALO COMMERCIAL 4" ROUND, RETROFIT FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4311.0 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581214

CATALOG NUMBER: HC4R55D010-HM44560930-42RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P581214

CATALOG NUMBER: HC4R55D010-HM44560930-42RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	488535
5°	498994
10°	518691
15°	518896
20°	479748
25°	414578
30°	337268
35°	247760
40°	143208
45°	66897
50°	30933
55°	10774
60°	3454
65°	2422
70°	1984
75°	1334
80°	0
85°	0



TEST NUMBER: P581214

CATALOG NUMBER: HC4R55D010-HM44560930-42RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	388.8	9.0
10°-20°	1126.2	26.1
20°-30°	1386.9	32.2
30°-40°	1012.5	23.5
40°-50°	330.0	7.7
50°-60°	55.2	1.3
60°-70°	8.5	0.2
70°-80°	2.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2901.8	67.3
0°-40°	3914.4	90.8
0°-60°	4299.5	99.7
0°-90°	4311.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4311.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3961	
5°	4030	389
15°	4064	1126
25°	3046	1387
35°	1645	1013
45°	384	330
55°	50	55
65°	8	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P581214

CATALOG NUMBER: HC4R55D010-HM44560930-42RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	3960.7
2.5°	3963.4
5°	4030.1
7.5°	4107.9
10°	4141.3
12.5°	4130.2
15°	4063.5
17.5°	3896.7
20°	3654.9
22.5°	3363.1
25°	3046.2
27.5°	2715.4
30°	2368.0
32.5°	2012.3
35°	1645.4
37.5°	1275.8
40°	889.4
42.5°	580.8
45°	383.5
47.5°	252.9
50°	161.2
52.5°	94.5
55°	50.1
57.5°	19.5
60°	14.0
62.5°	11.1
65°	8.3
67.5°	5.5
70°	5.5
72.5°	2.8
75°	2.8
77.5°	2.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)