

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581227

Luminaire Tested: **HC455D010-HM44560935-41WDBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC455D010-HM44560935-41WDBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3752.4 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581227

CATALOG NUMBER: HC455D010-HM44560935-41WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P581227

CATALOG NUMBER: HC455D010-HM44560935-41WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	374231
5°	374571
10°	375282
15°	380779
20°	371287
25°	348353
30°	308127
35°	234298
40°	147636
45°	84759
50°	44941
55°	18645
60°	4983
65°	4232
70°	3138
75°	2716
80°	2060
85°	4104



TEST NUMBER: P581227

CATALOG NUMBER: HC455D010-HM44560935-41WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	287.7	7.7
10°-20°	835.0	22.3
20°-30°	1165.3	31.1
30°-40°	958.9	25.6
40°-50°	395.0	10.5
50°-60°	89.0	2.4
60°-70°	14.3	0.4
70°-80°	5.3	0.1
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2287.9	61.0
0°-40°	3246.8	86.5
0°-60°	3730.8	99.4
0°-90°	3752.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3752.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3034	
5°	3025	288
15°	2982	835
25°	2560	1165
35°	1556	959
45°	486	395
55°	87	89
65°	14	14
75°	6	5
85°	3	2
90°	0	



TEST NUMBER: P581227

CATALOG NUMBER: HC455D010-HM44560935-41WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3034.0
2.5°	3019.5
5°	3025.2
7.5°	3013.8
10°	2996.3
12.5°	2987.7
15°	2981.9
17.5°	2929.8
20°	2828.6
22.5°	2701.4
25°	2559.6
27.5°	2388.9
30°	2163.4
32.5°	1885.7
35°	1556.0
37.5°	1223.4
40°	916.9
42.5°	668.1
45°	485.9
47.5°	347.1
50°	234.2
52.5°	147.5
55°	86.7
57.5°	43.4
60°	20.2
62.5°	17.3
65°	14.5
67.5°	11.6
70°	8.7
72.5°	5.7
75°	5.7
77.5°	2.9
80°	2.9
82.5°	2.9
85°	2.9
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)