

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581877

Luminaire Tested: **HC620D010-HM60525835-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC620D010-HM60525835-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2020.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581877

CATALOG NUMBER: HC620D010-HM60525835-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581877

CATALOG NUMBER: HC620D010-HM60525835-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75197
5°	74917
10°	73674
15°	72373
20°	69872
25°	66252
30°	60256
35°	48151
40°	32124
45°	22902
50°	19087
55°	16630
60°	15711
65°	14801
70°	13608
75°	12687
80°	11555
85°	10127



TEST NUMBER: P581877

CATALOG NUMBER: HC620D010-HM60525835-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.8	6.4
10°-20°	358.0	17.7
20°-30°	500.3	24.8
30°-40°	440.7	21.8
40°-50°	238.1	11.8
50°-60°	159.2	7.9
60°-70°	112.9	5.6
70°-80°	63.4	3.1
80°-90°	18.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	987.1	48.9
0°-40°	1427.9	70.7
0°-60°	1825.2	90.4
0°-90°	2020.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2020.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1372	
5°	1361	129
15°	1275	358
25°	1095	500
35°	720	441
45°	295	238
55°	174	159
65°	114	113
75°	60	63
85°	16	19
90°	0	



TEST NUMBER: P581877

CATALOG NUMBER: HC620D010-HM60525835-61MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1371.7
2.5°	1364.4
5°	1361.4
7.5°	1348.3
10°	1323.5
12.5°	1300.0
15°	1275.2
17.5°	1241.5
20°	1197.7
22.5°	1149.4
25°	1095.3
27.5°	1032.4
30°	951.9
32.5°	852.6
35°	719.5
37.5°	574.7
40°	448.9
42.5°	353.8
45°	295.4
47.5°	255.9
50°	223.8
52.5°	197.4
55°	174.0
57.5°	157.9
60°	143.3
62.5°	128.7
65°	114.1
67.5°	99.5
70°	84.9
72.5°	71.6
75°	59.9
77.5°	48.3
80°	36.6
82.5°	26.3
85°	16.1
87.5°	7.4
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)