

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581947

Luminaire Tested: **HC620D010-HM60525935-61MDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581947  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC620D010-HM60525935-61MDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1840.8 lumens  
Efficiency: N/A  
Efficacy: 92.0 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581947

CATALOG NUMBER: HC620D010-HM60525935-61MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581947

CATALOG NUMBER: HC620D010-HM60525935-61MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92197
5°	92120
10°	91158
15°	89331
20°	84620
25°	76414
30°	64915
35°	47930
40°	27716
45°	14715
50°	8307
55°	4339
60°	2840
65°	2024
70°	1459
75°	1101
80°	821
85°	755



TEST NUMBER: P581947

CATALOG NUMBER: HC620D010-HM60525935-61MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.6	8.6
10°-20°	440.2	23.9
20°-30°	574.6	31.2
30°-40°	439.1	23.9
40°-50°	159.0	8.6
50°-60°	46.1	2.5
60°-70°	16.5	0.9
70°-80°	5.6	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1173.5	63.7
0°-40°	1612.6	87.6
0°-60°	1817.6	98.7
0°-90°	1840.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1840.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1682	
5°	1674	159
15°	1574	440
25°	1263	575
35°	716	439
45°	190	159
55°	45	46
65°	16	16
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P581947

CATALOG NUMBER: HC620D010-HM60525935-61MDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1681.8
2.5°	1674.0
5°	1674.0
7.5°	1662.3
10°	1637.6
12.5°	1609.1
15°	1574.0
17.5°	1522.0
20°	1450.5
22.5°	1362.1
25°	1263.3
27.5°	1151.6
30°	1025.5
32.5°	883.9
35°	716.2
37.5°	540.7
40°	387.3
42.5°	267.7
45°	189.8
47.5°	136.4
50°	97.4
52.5°	68.9
55°	45.4
57.5°	32.5
60°	25.9
62.5°	20.8
65°	15.6
67.5°	13.0
70°	9.1
72.5°	6.5
75°	5.2
77.5°	3.9
80°	2.6
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)