

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581265

Luminaire Tested: **HC460D010-HM44560827-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560827-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4515.5 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581265

CATALOG NUMBER: HC460D010-HM44560827-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P581265

CATALOG NUMBER: HC460D010-HM44560827-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	584572
5°	572343
10°	540885
15°	505181
20°	462028
25°	412591
30°	346469
35°	243739
40°	150357
45°	90027
50°	53058
55°	26408
60°	13642
65°	8960
70°	5518
75°	4384
80°	2131
85°	4246



TEST NUMBER: P581265

CATALOG NUMBER: HC460D010-HM44560827-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	431.7	9.6
10°-20°	1105.9	24.5
20°-30°	1379.1	30.5
30°-40°	1015.9	22.5
40°-50°	417.8	9.3
50°-60°	122.1	2.7
60°-70°	31.4	0.7
70°-80°	9.7	0.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2916.6	64.6
0°-40°	3932.5	87.1
0°-60°	4472.4	99.0
0°-90°	4515.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4515.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4739	
5°	4622	432
15°	3956	1106
25°	3032	1379
35°	1619	1016
45°	516	418
55°	123	122
65°	31	31
75°	9	10
85°	3	2
90°	0	



TEST NUMBER: P581265

CATALOG NUMBER: HC460D010-HM44560827-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4739.3
2.5°	4690.1
5°	4622.5
7.5°	4499.7
10°	4318.5
12.5°	4140.3
15°	3956.1
17.5°	3750.3
20°	3519.9
22.5°	3280.3
25°	3031.6
27.5°	2755.1
30°	2432.6
32.5°	2042.6
35°	1618.7
37.5°	1244.0
40°	933.8
42.5°	691.1
45°	516.1
47.5°	380.8
50°	276.5
52.5°	190.4
55°	122.8
57.5°	73.8
60°	55.3
62.5°	39.9
65°	30.7
67.5°	21.5
70°	15.3
72.5°	12.3
75°	9.2
77.5°	6.1
80°	3.0
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)