

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581281

Luminaire Tested: **HC460D010-HM44560830-41WDBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581281  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC460D010-HM44560830-41WDBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4424.0 lumens  
Efficiency: N/A  
Efficacy: 80.4 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.03  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 55  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581281

CATALOG NUMBER: HC460D010-HM44560830-41WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P581281

CATALOG NUMBER: HC460D010-HM44560830-41WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	441207
5°	441617
10°	442465
15°	448931
20°	437731
25°	410699
30°	363275
35°	276234
40°	174059
45°	99935
50°	53000
55°	21999
60°	5896
65°	4962
70°	3715
75°	3241
80°	2415
85°	4812



TEST NUMBER: P581281

CATALOG NUMBER: HC460D010-HM44560830-41WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	339.2	7.7
10°-20°	984.4	22.3
20°-30°	1373.8	31.1
30°-40°	1130.5	25.6
40°-50°	465.7	10.5
50°-60°	104.9	2.4
60°-70°	16.8	0.4
70°-80°	6.3	0.1
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2697.4	61.0
0°-40°	3828.0	86.5
0°-60°	4398.6	99.4
0°-90°	4424.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4424.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3577	
5°	3567	339
15°	3516	984
25°	3018	1374
35°	1834	1131
45°	573	466
55°	102	105
65°	17	17
75°	7	6
85°	3	2
90°	0	



TEST NUMBER: P581281

CATALOG NUMBER: HC460D010-HM44560830-41WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3577.0
2.5°	3559.9
5°	3566.7
7.5°	3553.1
10°	3532.7
12.5°	3522.4
15°	3515.6
17.5°	3454.2
20°	3334.8
22.5°	3184.8
25°	3017.7
27.5°	2816.5
30°	2550.6
32.5°	2223.3
35°	1834.5
37.5°	1442.4
40°	1081.0
42.5°	787.7
45°	572.9
47.5°	409.2
50°	276.2
52.5°	173.9
55°	102.3
57.5°	51.1
60°	23.9
62.5°	20.4
65°	17.0
67.5°	13.6
70°	10.3
72.5°	6.8
75°	6.8
77.5°	3.4
80°	3.4
82.5°	3.4
85°	3.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)