

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581957

Luminaire Tested: **HC620D010-HM60525935-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC620D010-HM60525935-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1921.3 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581957

CATALOG NUMBER: HC620D010-HM60525935-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581957

CATALOG NUMBER: HC620D010-HM60525935-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75246
5°	75754
10°	76630
15°	78196
20°	78634
25°	76190
30°	69118
35°	56195
40°	37306
45°	20754
50°	11641
55°	6461
60°	3563
65°	2698
70°	1875
75°	1377
80°	821
85°	755



TEST NUMBER: P581957

CATALOG NUMBER: HC620D010-HM60525935-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.4	6.8
10°-20°	388.5	20.2
20°-30°	572.6	29.8
30°-40°	512.2	26.7
40°-50°	222.2	11.6
50°-60°	65.3	3.4
60°-70°	20.8	1.1
70°-80°	7.4	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1092.5	56.9
0°-40°	1604.7	83.5
0°-60°	1892.2	98.5
0°-90°	1921.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1921.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1373	
5°	1377	131
15°	1378	388
25°	1260	573
35°	840	512
45°	268	222
55°	68	65
65°	21	21
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P581957

CATALOG NUMBER: HC620D010-HM60525935-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1372.6
2.5°	1368.8
5°	1376.6
7.5°	1379.2
10°	1376.6
12.5°	1376.6
15°	1377.8
17.5°	1370.0
20°	1347.9
22.5°	1310.3
25°	1259.6
27.5°	1188.1
30°	1091.9
32.5°	977.6
35°	839.7
37.5°	682.4
40°	521.3
42.5°	380.9
45°	267.7
47.5°	191.1
50°	136.5
52.5°	97.4
55°	67.6
57.5°	45.5
60°	32.5
62.5°	25.9
65°	20.8
67.5°	15.6
70°	11.7
72.5°	9.1
75°	6.5
77.5°	5.2
80°	2.6
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)