

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581305

Luminaire Tested: **HC460D010-HM44560835-41MDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560835-41MDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5294.8 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.96
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581305
CATALOG NUMBER: HC460D010-HM44560835-41MDC

Luminous Intensity Polar Plot





TEST NUMBER: P581305

CATALOG NUMBER: HC460D010-HM44560835-41MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	72	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	60			
8	78	68	62	58	77	68	62	58	67	61	57	65	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52			
10	70	61	55	51	69	60	54	51	59	54	50	58	54	50	58	53	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	613287
5°	624557
10°	643802
15°	636683
20°	584626
25°	504361
30°	411017
35°	304347
40°	174590
45°	84393
50°	40182
55°	14021
60°	5082
65°	3006
70°	2488
75°	1620
80°	0
85°	0



TEST NUMBER: P581305

CATALOG NUMBER: HC460D010-HM44560835-41MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	485.2	9.2
10°-20°	1382.2	26.1
20°-30°	1687.9	31.9
30°-40°	1240.9	23.4
40°-50°	411.3	7.8
50°-60°	72.6	1.4
60°-70°	11.0	0.2
70°-80°	3.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3555.3	67.1
0°-40°	4796.2	90.6
0°-60°	5280.2	99.7
0°-90°	5294.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5294.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4972	
5°	5044	485
15°	4986	1382
25°	3706	1688
35°	2021	1241
45°	484	411
55°	65	73
65°	10	11
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P581305

CATALOG NUMBER: HC460D010-HM44560835-41MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4972.1
2.5°	4975.5
5°	5044.2
7.5°	5119.7
10°	5140.2
12.5°	5092.2
15°	4985.9
17.5°	4766.3
20°	4453.9
22.5°	4090.2
25°	3705.9
27.5°	3304.5
30°	2885.8
32.5°	2467.2
35°	2021.2
37.5°	1568.1
40°	1084.3
42.5°	717.2
45°	483.8
47.5°	322.6
50°	209.4
52.5°	123.5
55°	65.2
57.5°	27.4
60°	20.6
62.5°	13.8
65°	10.3
67.5°	6.9
70°	6.9
72.5°	3.4
75°	3.4
77.5°	3.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)