

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581965

Luminaire Tested: **HC620D010-HM60525940-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC620D010-HM60525940-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1864.0 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581965

CATALOG NUMBER: HC620D010-HM60525940-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P581965

CATALOG NUMBER: HC620D010-HM60525940-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	93353
5°	93275
10°	92300
15°	90449
20°	85676
25°	77375
30°	65725
35°	48526
40°	28060
45°	14901
50°	8418
55°	4406
60°	2884
65°	2037
70°	1475
75°	1101
80°	821
85°	881



TEST NUMBER: P581965

CATALOG NUMBER: HC620D010-HM60525940-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.6	8.6
10°-20°	445.7	23.9
20°-30°	581.8	31.2
30°-40°	444.6	23.9
40°-50°	161.0	8.6
50°-60°	46.8	2.5
60°-70°	16.7	0.9
70°-80°	5.7	0.3
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1188.1	63.7
0°-40°	1632.7	87.6
0°-60°	1840.5	98.7
0°-90°	1864.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1864.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1703	
5°	1695	161
15°	1594	446
25°	1279	582
35°	725	445
45°	192	161
55°	46	47
65°	16	17
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P581965

CATALOG NUMBER: HC620D010-HM60525940-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1702.9
2.5°	1695.0
5°	1695.0
7.5°	1683.2
10°	1658.1
12.5°	1629.1
15°	1593.7
17.5°	1541.0
20°	1468.6
22.5°	1379.2
25°	1279.2
27.5°	1166.0
30°	1038.3
32.5°	894.8
35°	725.1
37.5°	547.5
40°	392.1
42.5°	271.1
45°	192.2
47.5°	138.2
50°	98.7
52.5°	69.8
55°	46.1
57.5°	32.9
60°	26.3
62.5°	21.1
65°	15.7
67.5°	13.1
70°	9.2
72.5°	6.6
75°	5.2
77.5°	4.0
80°	2.6
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)