

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592946

Luminaire Tested: **HC460D010-HM44560850-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592946
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560850-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5746.7 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592946

CATALOG NUMBER: HC460D010-HM44560850-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P592946

CATALOG NUMBER: HC460D010-HM44560850-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	743959
5°	728414
10°	688365
15°	642915
20°	588000
25°	525075
30°	440941
35°	310189
40°	191336
45°	114553
50°	67508
55°	33612
60°	17367
65°	11412
70°	7032
75°	5576
80°	2770
85°	5519



TEST NUMBER: P592946

CATALOG NUMBER: HC460D010-HM44560850-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	549.4	9.6
10°-20°	1407.4	24.5
20°-30°	1755.1	30.5
30°-40°	1292.8	22.5
40°-50°	531.7	9.3
50°-60°	155.3	2.7
60°-70°	40.0	0.7
70°-80°	12.3	0.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3711.8	64.6
0°-40°	5004.7	87.1
0°-60°	5691.7	99.0
0°-90°	5746.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5746.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6032	
5°	5883	549
15°	5035	1407
25°	3858	1755
35°	2060	1293
45°	657	532
55°	156	155
65°	39	40
75°	12	12
85°	4	3
90°	0	



TEST NUMBER: P592946

CATALOG NUMBER: HC460D010-HM44560850-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6031.5
2.5°	5968.9
5°	5883.0
7.5°	5726.6
10°	5496.0
12.5°	5269.2
15°	5034.7
17.5°	4772.8
20°	4479.6
22.5°	4174.7
25°	3858.1
27.5°	3506.3
30°	3095.9
32.5°	2599.5
35°	2060.0
37.5°	1583.1
40°	1188.3
42.5°	879.5
45°	656.7
47.5°	484.7
50°	351.8
52.5°	242.4
55°	156.3
57.5°	93.8
60°	70.4
62.5°	50.8
65°	39.1
67.5°	27.4
70°	19.5
72.5°	15.7
75°	11.7
77.5°	7.8
80°	3.9
82.5°	3.9
85°	3.9
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)