

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581362

Luminaire Tested: **HC460D010-HM44560930-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560930-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4175.7 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581362

CATALOG NUMBER: HC460D010-HM44560930-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581362

CATALOG NUMBER: HC460D010-HM44560930-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			47
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	354014
5°	352135
10°	345698
15°	338422
20°	323954
25°	301237
30°	266610
35°	210432
40°	157458
45°	121129
50°	98268
55°	81503
60°	72108
65°	66690
70°	61561
75°	56569
80°	51356
85°	40900



TEST NUMBER: P581362

CATALOG NUMBER: HC460D010-HM44560930-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.9	6.4
10°-20°	743.2	17.8
20°-30°	1009.2	24.2
30°-40°	874.2	20.9
40°-50°	548.8	13.1
50°-60°	345.3	8.3
60°-70°	226.8	5.4
70°-80°	125.1	3.0
80°-90°	34.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2021.3	48.4
0°-40°	2895.5	69.3
0°-60°	3789.6	90.8
0°-90°	4175.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4175.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2870	
5°	2844	269
15°	2650	743
25°	2213	1009
35°	1398	874
45°	694	549
55°	379	345
65°	228	227
75°	119	125
85°	29	34
90°	0	



TEST NUMBER: P581362

CATALOG NUMBER: HC460D010-HM44560930-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2870.1
2.5°	2852.7
5°	2844.0
7.5°	2815.1
10°	2760.1
12.5°	2705.2
15°	2650.2
17.5°	2575.0
20°	2468.0
22.5°	2346.5
25°	2213.4
27.5°	2060.0
30°	1871.9
32.5°	1643.4
35°	1397.5
37.5°	1171.8
40°	977.9
42.5°	824.6
45°	694.4
47.5°	596.0
50°	512.1
52.5°	439.8
55°	379.0
57.5°	326.9
60°	292.3
62.5°	260.3
65°	228.5
67.5°	196.7
70°	170.7
72.5°	141.8
75°	118.7
77.5°	92.6
80°	72.3
82.5°	49.2
85°	28.9
87.5°	11.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)