

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581363

Luminaire Tested: **HC460D010-HM44560930-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560930-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3979.1 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581363

CATALOG NUMBER: HC460D010-HM44560930-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P581363

CATALOG NUMBER: HC460D010-HM44560930-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58			58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52			52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48			48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41			41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	349574
5°	346972
10°	337945
15°	329049
20°	314306
25°	292840
30°	257850
35°	203370
40°	147604
45°	108465
50°	88232
55°	74019
60°	67051
65°	61641
70°	57342
75°	52375
80°	47307
85°	40900



TEST NUMBER: P581363

CATALOG NUMBER: HC460D010-HM44560930-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.2	6.6
10°-20°	722.7	18.2
20°-30°	979.8	24.6
30°-40°	840.7	21.1
40°-50°	496.4	12.5
50°-60°	314.6	7.9
60°-70°	211.4	5.3
70°-80°	116.6	2.9
80°-90°	32.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1966.7	49.4
0°-40°	2807.4	70.6
0°-60°	3618.4	90.9
0°-90°	3979.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3979.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2834	
5°	2802	264
15°	2577	723
25°	2152	980
35°	1351	841
45°	622	496
55°	344	315
65°	211	211
75°	110	117
85°	29	33
90°	0	



TEST NUMBER: P581363

CATALOG NUMBER: HC460D010-HM44560930-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2834.1
2.5°	2813.9
5°	2802.3
7.5°	2764.7
10°	2698.2
12.5°	2640.4
15°	2576.8
17.5°	2495.8
20°	2394.5
22.5°	2281.8
25°	2151.7
27.5°	1998.4
30°	1810.4
32.5°	1587.7
35°	1350.6
37.5°	1122.1
40°	916.7
42.5°	746.2
45°	621.8
47.5°	532.1
50°	459.8
52.5°	399.1
55°	344.2
57.5°	300.7
60°	271.8
62.5°	243.0
65°	211.2
67.5°	185.1
70°	159.0
72.5°	133.0
75°	109.9
77.5°	86.7
80°	66.6
82.5°	46.2
85°	28.9
87.5°	11.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)