

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581392

Luminaire Tested: **HC460D010-HM44560940-41NDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560940-41NDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4145.2 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581392

CATALOG NUMBER: HC460D010-HM44560940-41NDH

Luminous Intensity Polar Plot





TEST NUMBER: P581392

CATALOG NUMBER: HC460D010-HM44560940-41NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	63	63	63	63
7	81	72	65	61	80	71	65	61	70	64	60	68	64	60	67	63	60	58	58	58	58
8	77	67	61	57	76	67	61	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	537651
5°	527880
10°	500706
15°	468175
20°	425209
25°	376253
30°	312955
35°	225685
40°	140857
45°	81253
50°	45824
55°	21827
60°	12532
65°	9573
70°	6455
75°	4241
80°	4262
85°	4104



TEST NUMBER: P581392

CATALOG NUMBER: HC460D010-HM44560940-41NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	398.5	9.6
10°-20°	1022.8	24.7
20°-30°	1257.9	30.3
30°-40°	934.2	22.5
40°-50°	379.8	9.2
50°-60°	105.1	2.5
60°-70°	32.8	0.8
70°-80°	11.0	0.3
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2679.2	64.6
0°-40°	3613.4	87.2
0°-60°	4098.3	98.9
0°-90°	4145.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4145.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4359	
5°	4263	399
15°	3666	1023
25°	2765	1258
35°	1499	934
45°	466	380
55°	102	105
65°	33	33
75°	9	11
85°	3	3
90°	0	



TEST NUMBER: P581392

CATALOG NUMBER: HC460D010-HM44560940-41NDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4358.9
2.5°	4317.2
5°	4263.4
7.5°	4156.0
10°	3997.7
12.5°	3833.5
15°	3666.3
17.5°	3466.2
20°	3239.4
22.5°	3009.5
25°	2764.6
27.5°	2499.0
30°	2197.3
32.5°	1854.1
35°	1498.8
37.5°	1164.4
40°	874.8
42.5°	638.9
45°	465.8
47.5°	334.3
50°	238.8
52.5°	164.2
55°	101.5
57.5°	65.6
60°	50.8
62.5°	41.8
65°	32.8
67.5°	23.9
70°	17.9
72.5°	14.9
75°	8.9
77.5°	6.0
80°	6.0
82.5°	2.9
85°	2.9
87.5°	2.9
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)