

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582046

Luminaire Tested: **HC625D010-HM60525840-61WDBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582046  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC625D010-HM60525840-61WDBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2562.4 lumens  
Efficiency: N/A  
Efficacy: 95.6 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582046

CATALOG NUMBER: HC625D010-HM60525840-61WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P582046

CATALOG NUMBER: HC625D010-HM60525840-61WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98  | 97  | 97  | 95  | 94  | 92  | 92  | 92  | 92  |
| 2   | 107 | 101 | 97  | 93  | 104 | 100 | 95  | 92  | 96  | 93  | 90  | 93  | 91  | 88  | 90  | 88  | 86  | 85  | 85  | 85  | 85  |
| 3   | 100 | 93  | 88  | 83  | 98  | 92  | 87  | 83  | 89  | 85  | 81  | 87  | 83  | 80  | 84  | 81  | 79  | 77  | 77  | 77  | 77  |
| 4   | 95  | 86  | 80  | 75  | 93  | 85  | 79  | 75  | 83  | 78  | 74  | 81  | 77  | 73  | 79  | 75  | 72  | 71  | 71  | 71  | 71  |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 72  | 67  | 75  | 70  | 67  | 73  | 69  | 66  | 65  | 65  | 65  | 65  |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 62  | 70  | 65  | 61  | 69  | 64  | 61  | 59  | 59  | 59  | 59  |
| 7   | 79  | 68  | 62  | 57  | 77  | 68  | 61  | 57  | 66  | 61  | 57  | 65  | 60  | 56  | 64  | 59  | 56  | 54  | 54  | 54  | 54  |
| 8   | 74  | 64  | 57  | 52  | 73  | 63  | 57  | 52  | 62  | 56  | 52  | 61  | 56  | 52  | 60  | 55  | 52  | 50  | 50  | 50  | 50  |
| 9   | 70  | 59  | 53  | 48  | 69  | 59  | 53  | 48  | 58  | 52  | 48  | 57  | 52  | 48  | 56  | 51  | 48  | 46  | 46  | 46  | 46  |
| 10  | 66  | 56  | 49  | 45  | 65  | 55  | 49  | 45  | 54  | 48  | 45  | 53  | 48  | 44  | 53  | 48  | 44  | 43  | 43  | 43  | 43  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 91007  |
| 5°  | 91674  |
| 10° | 93274  |
| 15° | 96970  |
| 20° | 101036 |
| 25° | 104643 |
| 30° | 103237 |
| 35° | 86016  |
| 40° | 55160  |
| 45° | 27553  |
| 50° | 10934  |
| 55° | 3708   |
| 60° | 1053   |
| 65° | 752    |
| 70° | 625    |
| 75° | 826    |
| 80° | 600    |
| 85° | 0      |



TEST NUMBER: P582046

CATALOG NUMBER: HC625D010-HM60525840-61WDBB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 159.3  | 6.2       |
| 10°-20°   | 484.6  | 18.9      |
| 20°-30°   | 791.3  | 30.9      |
| 30°-40°   | 775.7  | 30.3      |
| 40°-50°   | 297.4  | 11.6      |
| 50°-60°   | 43.6   | 1.7       |
| 60°-70°   | 6.5    | 0.3       |
| 70°-80°   | 3.3    | 0.1       |
| 80°-90°   | 0.8    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1435.2 | 56.0      |
| 0°-40°    | 2210.9 | 86.3      |
| 0°-60°    | 2551.9 | 99.6      |
| 0°-90°    | 2562.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2562.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1660 |      |
| 5°  | 1666 | 159  |
| 15° | 1709 | 485  |
| 25° | 1730 | 791  |
| 35° | 1285 | 776  |
| 45° | 355  | 297  |
| 55° | 39   | 44   |
| 65° | 6    | 6    |
| 75° | 4    | 3    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P582046

CATALOG NUMBER: HC625D010-HM60525840-61WDBB

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1660.1 |
| 2.5°  | 1656.2 |
| 5°    | 1665.9 |
| 7.5°  | 1671.8 |
| 10°   | 1675.6 |
| 12.5° | 1689.2 |
| 15°   | 1708.6 |
| 17.5° | 1724.1 |
| 20°   | 1731.9 |
| 22.5° | 1733.9 |
| 25°   | 1730.0 |
| 27.5° | 1702.8 |
| 30°   | 1630.9 |
| 32.5° | 1495.1 |
| 35°   | 1285.3 |
| 37.5° | 1027.1 |
| 40°   | 770.8  |
| 42.5° | 549.4  |
| 45°   | 355.4  |
| 47.5° | 217.5  |
| 50°   | 128.2  |
| 52.5° | 73.8   |
| 55°   | 38.8   |
| 57.5° | 17.4   |
| 60°   | 9.6    |
| 62.5° | 7.8    |
| 65°   | 5.8    |
| 67.5° | 5.8    |
| 70°   | 3.9    |
| 72.5° | 3.9    |
| 75°   | 3.9    |
| 77.5° | 1.9    |
| 80°   | 1.9    |
| 82.5° | 1.9    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)