

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581399

Luminaire Tested: **HC460D010-HM44560940-41NDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC460D010-HM44560940-41NDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4109.6 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581399

CATALOG NUMBER: HC460D010-HM44560940-41NDW

Luminous Intensity Polar Plot





TEST NUMBER: P581399

CATALOG NUMBER: HC460D010-HM44560940-41NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	104	101	109	105	102	100	101	99	97	98	96	94	94	92	91	89	89	89	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71	71	71	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64	64	64	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	58	58	58	58
6	79	68	61	56	78	67	60	55	66	60	55	64	59	55	63	58	54	52	52	52	52
7	75	63	56	51	73	62	56	51	61	55	50	60	54	50	59	53	50	48	48	48	48
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44	44	44	44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41	41	41	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38	38	38	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	361033
5°	358351
10°	349030
15°	339827
20°	324610
25°	302434
30°	266310
35°	210040
40°	152450
45°	112023
50°	91129
55°	76428
60°	69271
65°	63626
70°	59217
75°	54091
80°	48799
85°	42315



TEST NUMBER: P581399

CATALOG NUMBER: HC460D010-HM44560940-41NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.9	6.6
10°-20°	746.4	18.2
20°-30°	1011.9	24.6
30°-40°	868.3	21.1
40°-50°	512.7	12.5
50°-60°	324.9	7.9
60°-70°	218.3	5.3
70°-80°	120.5	2.9
80°-90°	33.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2031.2	49.4
0°-40°	2899.5	70.6
0°-60°	3737.1	90.9
0°-90°	4109.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4109.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2927	
5°	2894	273
15°	2661	746
25°	2222	1012
35°	1395	868
45°	642	513
55°	355	325
65°	218	218
75°	114	120
85°	30	34
90°	0	



TEST NUMBER: P581399

CATALOG NUMBER: HC460D010-HM44560940-41NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2927.0
2.5°	2906.2
5°	2894.2
7.5°	2855.4
10°	2786.7
12.5°	2726.9
15°	2661.2
17.5°	2577.6
20°	2473.0
22.5°	2356.6
25°	2222.2
27.5°	2063.9
30°	1869.8
32.5°	1639.8
35°	1394.9
37.5°	1158.9
40°	946.8
42.5°	770.5
45°	642.2
47.5°	549.6
50°	474.9
52.5°	412.2
55°	355.4
57.5°	310.7
60°	280.8
62.5°	250.9
65°	218.0
67.5°	191.2
70°	164.2
72.5°	137.4
75°	113.5
77.5°	89.6
80°	68.7
82.5°	47.8
85°	29.9
87.5°	12.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)