

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582037

Luminaire Tested: **HC625D010-HM60525840-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC625D010-HM60525840-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3061.4 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582037

CATALOG NUMBER: HC625D010-HM60525840-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P582037

CATALOG NUMBER: HC625D010-HM60525840-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61		
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57		
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54		
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145383
5°	147639
10°	156048
15°	173758
20°	180196
25°	147843
30°	103592
35°	70684
40°	36819
45°	12939
50°	5791
55°	1854
60°	1053
65°	752
70°	625
75°	402
80°	0
85°	0



TEST NUMBER: P582037

CATALOG NUMBER: HC625D010-HM60525840-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.9	8.5
10°-20°	861.0	28.1
20°-30°	1096.3	35.8
30°-40°	653.4	21.3
40°-50°	158.5	5.2
50°-60°	24.3	0.8
60°-70°	6.0	0.2
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2217.2	72.4
0°-40°	2870.6	93.8
0°-60°	3053.4	99.7
0°-90°	3061.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3061.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2652	
5°	2683	260
15°	3062	861
25°	2444	1096
35°	1056	653
45°	167	158
55°	19	24
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582037

CATALOG NUMBER: HC625D010-HM60525840-61MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2652.0
2.5°	2652.0
5°	2682.9
7.5°	2731.5
10°	2803.3
12.5°	2916.0
15°	3061.6
17.5°	3152.8
20°	3088.8
22.5°	2842.2
25°	2444.2
27.5°	2005.4
30°	1636.5
32.5°	1337.6
35°	1056.2
37.5°	778.5
40°	514.5
42.5°	277.7
45°	166.9
47.5°	104.9
50°	67.9
52.5°	40.7
55°	19.4
57.5°	11.7
60°	9.6
62.5°	7.8
65°	5.8
67.5°	3.9
70°	3.9
72.5°	1.9
75°	1.9
77.5°	1.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)