

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581411

Luminaire Tested: **HC407D010-HM40525827-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581411
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC407D010-HM40525827-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 843.2 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581411

CATALOG NUMBER: HC407D010-HM40525827-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581411

CATALOG NUMBER: HC407D010-HM40525827-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70887
5°	71430
10°	72318
15°	74128
20°	74675
25°	72540
30°	66499
35°	54735
40°	39884
45°	25886
50°	14584
55°	6924
60°	2714
65°	1693
70°	1154
75°	763
80°	426
85°	849



TEST NUMBER: P581411

CATALOG NUMBER: HC407D010-HM40525827-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.1	6.5
10°-20°	163.7	19.4
20°-30°	242.7	28.8
30°-40°	224.2	26.6
40°-50°	117.0	13.9
50°-60°	32.1	3.8
60°-70°	6.2	0.7
70°-80°	1.8	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.5	54.7
0°-40°	685.7	81.3
0°-60°	834.8	99.0
0°-90°	843.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	843.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	575	
5°	577	55
15°	580	164
25°	533	243
35°	364	224
45°	148	117
55°	32	32
65°	6	6
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P581411

CATALOG NUMBER: HC407D010-HM40525827-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	574.7
2.5°	573.1
5°	576.9
7.5°	578.4
10°	577.4
12.5°	578.4
15°	580.5
17.5°	578.4
20°	568.9
22.5°	553.6
25°	533.0
27.5°	505.0
30°	466.9
32.5°	418.9
35°	363.5
37.5°	305.3
40°	247.7
42.5°	194.9
45°	148.4
47.5°	108.8
50°	76.0
52.5°	50.8
55°	32.2
57.5°	19.0
60°	11.0
62.5°	8.0
65°	5.8
67.5°	4.2
70°	3.2
72.5°	2.2
75°	1.6
77.5°	1.0
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)